

# PCB TERMINAL BLOCKS

## 10mm Pitch 18 Pole Rising Clamp Terminal Blocks

PCB  
TERMINAL  
BLOCKS

INTER-  
CONNECTION

FUSES &  
FUSE-  
HOLDERS

LEDs &  
INDICATORS

MINIATURE  
SWITCHES

LIMIT &  
SAFETY  
SWITCHES

CONTROL  
PRODUCTS

INTERFACE  
MODULES &  
SUPPORTS


RELAY  
BASES

DIN RAIL  
ENCLOSURES

BATTERIES

SOLAR  
PANELS

TRANS-  
FORMERS

- Unique 18 pole strip
- Easily cut to required number of poles
- Can be supplied pre-cut
- Moulded in grey UL94-V0 flame retardant PC
- Professional rising clamp terminals
- 0.2-4.0mm<sup>2</sup> (30-12AWG) solid cable
- 0.2-2.5mm<sup>2</sup> (30-12AWG) stranded cable
- Guided pin alignment
- Captive screws
- Anti solder wicking terminals
-  approved


CTB8000



TYPE NO.	POLES	LENGTH
CTB8000/1	1	5mm
CTB8000/2	2	15mm
CTB8000/3	3	25mm
CTB8000/4	4	35mm
CTB8000/5	5	45mm
CTB8000/6	6	55mm
CTB8000/7	7	65mm
CTB8000/8	8	75mm
CTB8000/9	9	85mm
CTB8000/10	10	95mm
CTB8000/11	11	105mm
CTB8000/12	12	115mm
CTB8000/18	18	175mm

### SPECIFICATION

Rating	22A/500V
	UL=16A/300V, VDE&IMQ=22A/750V
Dielectric strength	≥3kV
Impulse withstand voltage	6kV
Working temperature	85°C
Moulding	UL94-V0 flame retardant PC
Pin/terminal	Tinned, nickel plated brass
Rising clamp	Zinc plated steel
Screw/torque	M2.5 steel zinc plated, 0.5Nm
Recommended PCB hole size	ø1.3mm



CAMDENBOSS

We operate a constant improvement policy, our products are subject to change without notice.

Ver 1.1

+44 (0)1638 716101  
info@camdenboss.com  
www.camdenboss.com



FM 28614 EMS 613558