

Centre drill set HSSE TiN Type A

For universal use up to 1300 N/mm²

ATORN[®]

Application

For centre drilling on conventional and CNC machines.

Version

- spiral-fluted design with grinding relief in metal box



Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	40	20	20	15	10	50	80	40	30	35	30	20	10	20	5	5	5		

Art. No.	11004 900
Countersink angle	60 Degree
Cutting material	HSSE
Surface	TiN
Form	A
Tool holding device	HA parallel shank
Composition of set	1 each of diameter 1.0/1.6/5 mm, 2 each of diameter 2.0/2.5/4 mm, 3 each of diameter 3.15 mm
DIN	333

EAN-Code

4050293012064