

Boring bar holder type E2

Application:

For clamping boring bars on lathes.

Version:

- For NC lathes
- For external and internal coolant supply
- Burnished
- tool chucks in accordance with DIN 69880/VDI 3425



Art. no.	22770 220
VDI mount diameter	20
Clamping diameter	20 mm
Outer diameter	50 mm
Projecting length	50 mm
Coolant supply	Yes