

Thread limit plug gauge with depth measurement

for standard metric ISO thread, scale interval 0.5 mm

leitech

Application:

For testing threads and measuring thread depths in one pass.

Execution:

- Thread inserts hardened and ground
- Black anodised aluminium housing
- Brushed chromium-plated scale
- Direct reading of the thread depth up to three times the thread diameter
- Measuring depth gradation of 0.5 mm on the scale sleeve



Art. no.	32850 200
Brand	LEITECH
Manufacturer Part Number	602907
Thread type	Metric thread
Thread type x nominal diameter x pitch	M20 x 2.5
Tolerance class	6H
Measuring depth	86 mm
Reading Length Metrology	0,5 mm
Handle size	T 600
DIN	13
Gross Weight	0.500 kg
Product Group	324