

Diamond plate boxes

Made from aluminium

Execution:

- Stainless steel latches and hinges
- 4 feet with M10 internal thread for mounting on loading surface
- 3.0 mm aluminium diamond plate
- All-round welded seams
- Gas pressure damper for easy opening of the lid
- Rubber seal on all sides and rebound straps on flip lid
- Safety carry handles



Art. no.	50017 403
Model	R70
Volume	70 l
External length	522 mm
External width	375 mm
External height	420 mm
Internal length	500 mm
Internal width	350 mm
Interior height	400 mm
With lid	Yes
With handle	Yes
With rollers	No
Lock type	Lever release fastener
Protected against dust/splash water	Yes
Material	Aluminium
Colour	Silver
Gross Weight	8.600 kg
Product Group	5AG