


Dimensions





Model Number

CE

GLV18-6/25/103/159

Retroreflective sensor

with 3-pin, M12 x 1 plastic connector

C


Features

Efficient Line in a short M18 plastic ٠ housing for standard applications

- Very high detection range ٠
- 4 LEDs indicator for 360° visibility •
- Optimized potentiometer design for a clear control button layout in the application
- Version with front optical face
- DC voltage version ٠

Product information

The GLV/GLK18 series sensors help improve the efficiency of machines and systems. The design of the M18 plastic housing, the connection technology, and sensor properties are highly standardized. Concentrating on the key sensor requirements has produced a robust and reliable product series for DC and AC/DC voltage systems without any overengineering. The mounting set included in the scope of delivery and the optimized potentiometer design ensure fast assembly and easy configuration.




Electrical connection





Indicators/operating means



1	Operating display	green
2	Signal display	yellow
4	Emitter	ł
5	Receiver	

Subject to modifications without notice Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

fa-info@pepperl-fuchs.com

Germany: +49 621 776-4411

Copyright Pepperl+Fuchs Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Technical data			Accessories
General specifications			CPZ18B03
Effective detection range		0 6.5 m	
Reflector distance		0.05 6.5 m	Mounting Bracket with swivel nut
Threshold detection range		8 m	BF 18
Reference target		reflector C110-2	Mounting flange, 18 mm
Light source		LED	Mounting nango, to min
Light type		modulated visible red light , 640 nm	BF 18-F
Diameter of the light spot		approx. 300 mm at 8 m	Mounting flange with dead stop, 18 m
Angle of divergence		approx. 2 °	
Optical face		frontal	BF 5-30
Ambient light limit		30000 Lux	Universal mounting bracket for cylindric
Functional safety related para	meters		sensors with a diameter of 5 30 mm
MTTF _d		920 a	
Mission Time (T _M)		20 a	V11-G-2M-PUR
Diagnostic Coverage (DC)		0 %	Cable socket, M12, 3-pin, PUR cable
Indicators/operating means			V11-W-2M-PUR
Operating display		LED green, statically lit Power on	Cable socket, M12, 3-pin, PUR cable
Function display		LED yellow: lights up when receiving the light beam ; flashes	
		when falling short of the stability control; OFF when light beam is interrupted	Other suitable accessories can be found www.pepperl-fuchs.com
Electrical specifications			
Operating voltage	UB	10 30 V DC	
No-load supply current	I ₀	< 20 mA	
Output			
Switching type		light on	
Signal output		1 PNP, short-circuit protected, open collector	
Switching voltage		max. 30 V DC	
Switching current		max. 100 mA	
Voltage drop	U _d	≤ 1.5 V DC	
Switching frequency	f	500 Hz	
Response time		≤ 1 ms	
Ambient conditions			
Ambient temperature		-25 60 °C (-13 140 °F)	
Storage temperature		-40 70 °C (-40 158 °F)	
Mechanical specifications			
Protection degree		IP67	
Connection		Connector M12 x 1, 3-pin	
Material		· ·	
Housing		PC	
Optical face		PMMA	
Connector		plastic	
Mass		approx. 10 g	
Compliance with standards an ves	d direc	ti-	
Standard conformity			
Product standard		EN 60947-5-2:2007 IEC 60947-5-2:2007	
Approvals and certificates			
Protection class		II, rated insulation voltage \leq 250 V AC with pollution degree 1-2 according to IEC 60664-1	
UL approval		cULus Listed, Class 2 Power Source	
CCC approval		Products with a maximum operating voltage of \leq 36 V do not bear a CCC marking because they do not require approval.	


Date of issue: 2013-01-23 193024_eng.xml Release date: 2013-01-09 08:58


Subject to modifications without no	otice

2

Copyright Pepperl+Fuchs Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

Curves/Diagrams





Subject to modifications without notice Pepperl+Fuchs Group

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com www.pepperl-fuchs.com

