Connection Line M12 × 1; 4-pin

S27-2MPUR

Part Number





wenglor

Technical Data

Mechanical Data		
Connection 1	Socket, angled	
Connection mode 1	M12 × 1, 4-pin	
Connection 2	stripped	
Torque	M12: 0,6 Nm	
Cable Length	2 m	
Cable Diameter	4,7 mm	
Wire cross-section	0,34 mm ²	
Display	LED	
Degree of Protection	IP67	
Temperature Range	-2580 °C	
Cable Jacket Material	PUR	
Material Wire Insulation	PP	
Material Sleeve Nut	CuZn, nickel-plated	
Halogen-free	yes	
Drag Chain Suitable	yes	
Bending radius (fixed installation)	5 × d	
Bending radius (used in motion)	10 × d	
Travel speed (with 5 m horizontal travel distance)	≤ 3,3 m/s	
Acceleration	≤ 5 m/s²	
Bending cycles	≤ 5000000	
Packaging unit	1 Piece	
Connection Diagram No.	S03	
Connection Equipment No.	2	

- Halogen free, drag chain suitability
- PUR, with LED, angled







E/A Output/input programmable

TO-Link

PoE Power over Ethernet
IN Safety Input

DSSD Safety Output
Signal Signal Output

BI_D+/- Ethernet Gigabit bidirect. data line (A-D)

EN0essez Encoder 0-pulse 0-5 (TTL)

Legend

Awv	Valve Output
а	Valve Control Output +
b	Valve Control Output 0 V
SY	Synchronization
SY-	Ground for the Synchronization
E+	Receiver-Line
S+	Emitter-Line
÷	Grounding
SnR	Switching Distance Reduction
	Ethernet Receive Path
Tx+/-	Ethernet Send Path
Bus	Interfaces-Bus A(+)/B(-)
La	Emitted Light disengageable
Mag	Magnet activation
RES	Input confirmation
EDM	Contactor Monitoring

ENA	Encoder A
ENB	Encoder B
Amin	Digital output MIN
Амах	Digital output MAX
Аок	Digital output OK
SY In	Synchronization In
SY OUT	Synchronization OUT
OLT	Brightness output
М	Maintenance
rsv	reserved
Wire Co	olors according to DIN IEC 757
BK	Black
BN	Brown
RD	Red
OG	Orange
YE	Yellow
GN	Green
BU	Blue
VT	Violet
GY	Grey
WH	White
PK	Pink

GNYE Green/Yellow

ENARS422 Encoder A/Ā (TTL)
ENBRS422 Encoder B/Ā (TTL)



