

## Roughing cutter, HSSE Co 5

6 cutting edges, uncoated

**ORION**<sup>®</sup>

### Application:

End mill for universal machining.

### Execution:

- HSSE Co 5
- With Morse taper and internal draw-in thread (from MT 4 with collar and driving surface in accordance with DIN 2207).
- type NR
- roughing teeth
- 25° twist angle



<b>Art. no.</b>	<b>15351 300</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	15351300
<b>Cutting material</b>	HSSE Co5
<b>Surface</b>	Uncoated
<b>Type</b>	NR
<b>Number of cutting edges</b>	6 PCS
<b>Twist angle</b>	25°
<b>Edge protection chamfer length</b>	0.2 mm
<b>Tool holding device</b>	Morse taper shank
<b>Construction length</b>	Normal
<b>Cutting edge diameter</b>	30 mm
<b>Cutting edge length</b>	45 mm
<b>Length</b>	147 mm
<b>Morse taper size</b>	MK 3
<b>Female thread</b>	12 mm
<b>fz steel 700</b>	0.08 mm
<b>Gross Weight</b>	0.400 kg
<b>Product Group</b>	106

### EAN

4039247096022