

## Dial gauge micrometer

Mitutoyo

### Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

### Execution:

- For direct GO/NG assessment of serial parts using an analogue or digital dial gauge
- 3-mm anvil stroke
- Brushed chromium-plated scale drum and sleeve
- Measuring faces carbide-tipped and micro-lapped

### Advantage:

- A moving anvil enables quick measurements

### Delivery:

Includes box, setting gauge (from 25 mm), adjustment wrench, excludes dial gauge



<b>Art. no.</b>	<b>32016 203</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	107-206
<b>Min./max. length measuring range</b>	125-150 mm
<b>Digit increment, micrometer</b>	0.01 mm
<b>Repeat accuracy</b>	2 µm
<b>Measuring spindle increments</b>	0.5 mm
<b>Spindle clamping</b>	Yes
<b>Measurement force</b>	10 N
<b>Measuring surface diameter</b>	6.35 mm
<b>Calibration Group</b>	AN
<b>Gross Weight</b>	1.425 kg
<b>Product Group</b>	3MA

### EAN

4946368440637