

## HSSE centre drill, extra long

For universal use up to 1000 N/mm<sup>2</sup>

**ATORN**<sup>®</sup>



### Application

For centre drilling on conventional and CNC machines on low-lying or difficult-to-access components.

### Version

- spiral-fluted design with relief grinding

### Advantage

- Extra length permits precise drilling, even on difficult-to-access components
- Radial relief ensures optimum chip breaking

Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	40	20	10	10		50	80	40	35	35	30	20	10	20					

<b>Art. No.</b>	<b>11014 100</b>
<b>Countersink angle</b>	60 Degree
<b>Cutting material</b>	HSSE
<b>Surface</b>	Uncoated
<b>Form</b>	A
<b>Tool holding device</b>	HA parallel shank
<b>Cutting edge diameter</b>	2.5 mm
<b>Shaft diameter</b>	8 mm
<b>Min./max cutting edge length</b>	3.1-3.6 mm
<b>Length</b>	120 mm
<b>f steel 700</b>	0.05 mm/U
<b>DIN</b>	333

### EAN-Code

4050293012453