

ITEM	MOLEX P/N	DESCRIPTION	QTY	UOM
A	39014021	MiniFit Jr SR Recpt Hsg 2 CKT V-0	1	PC
B	39000077	MiniFit Term Crp Fem Chn Bs Tin 16awg	2	PC
C	--	RESIN TPE NAT SANTOPRENE	A/R	KG
D	--	MOLD PART INNER CAP	2	PC
E	--	MASTER BATCH BLACK COLOR	A/R	KG

FROM	TO	CABLE DESCRIPTION	COLOR
A1	--	2CX16AWG UNSHD BK UL2464	BLACK
A2	--		RED




TABLE		
PART NUMBER	TITLE	L1
2171590205	2 CKT OVERMOLD MINIFIT JR PIGTAIL 500MM	500±10
2171590210	2 CKT OVERMOLD MINIFIT JR PIGTAIL 1M	1000±20
2171590220	2 CKT OVERMOLD MINIFIT JR PIGTAIL 2M	2000±25
2171590230	2 CKT OVERMOLD MINIFIT JR PIGTAIL 3M	3000±30

NOTES:

- MOLDING MATERIAL:
  - INNERCAP: PA66 NYLON RESIN.
  - OVERMOLD: SANTOPRENE TPE RESIN & MASTER BATCH BLACK
- ELECTRICAL PERFORMANCE:
  - VOLTAGE RATING: 300V AC.
  - THIS PRODUCT MUST PASS 100% CONTINUITY TEST PER MOLEX ES-36586-004.
    - DIELECTRONIC STRENGTH: 500V DC/0.01 SEC.
    - INSULATION RESISTANCE: 20M OHMS
- CONNECTOR VIEWS ARE SHOWN FROM MATING SIDE.
- MECHANICAL PERFORMANCE:
  - CABLE HARNESS SHOULD WITHSTAND AN AXIAL FORCE OF 5KGF FOR ONE MINUTE BETWEEN OVERMOLD AND CONNECTOR WITHOUT PHYSICAL DAMAGE.
  - OVERMOLD SIDE CAN PASS THE BENDING TEST IN 100 CYCLES AT EACH OF 2 PLANES, PER EIA364-41 CONDITION I.

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	CURRENT REV DESC:		<b>molex</b>																																							
	<table border="1"> <tr> <th>DIMENSION UNITS</th> <th>SCALE</th> </tr> <tr> <td>mm</td> <td>NTS</td> </tr> </table>	DIMENSION UNITS	SCALE		mm	NTS	<table border="1"> <tr> <th colspan="4">GENERAL TOLERANCES (UNLESS SPECIFIED)</th> </tr> <tr> <td>ANGULAR TOL</td> <td>±</td> <td colspan="2">°</td> </tr> <tr> <td>4 PLACES</td> <td>±</td> <td colspan="2"></td> </tr> <tr> <td>3 PLACES</td> <td>±</td> <td colspan="2"></td> </tr> <tr> <td>2 PLACES</td> <td>±</td> <td colspan="2"></td> </tr> <tr> <td>1 PLACE</td> <td>±</td> <td colspan="2"></td> </tr> <tr> <td>0 PLACES</td> <td>±</td> <td colspan="2"></td> </tr> </table>		GENERAL TOLERANCES (UNLESS SPECIFIED)				ANGULAR TOL	±	°		4 PLACES	±			3 PLACES	±			2 PLACES	±			1 PLACE	±			0 PLACES	±			<table border="1"> <tr> <td>EC NO: 662617</td> <td>2021/05/02</td> </tr> <tr> <td>DRWN: SBS04</td> <td>2021/05/10</td> </tr> <tr> <td>CHK'D: MNARAYAN01</td> <td>2021/05/10</td> </tr> <tr> <td>APPR: MNARAYAN01</td> <td>2021/05/10</td> </tr> </table>	EC NO: 662617	2021/05/02	DRWN: SBS04	2021/05/10	CHK'D: MNARAYAN01	2021/05/10
DIMENSION UNITS	SCALE																																										
mm	NTS																																										
GENERAL TOLERANCES (UNLESS SPECIFIED)																																											
ANGULAR TOL	±	°																																									
4 PLACES	±																																										
3 PLACES	±																																										
2 PLACES	±																																										
1 PLACE	±																																										
0 PLACES	±																																										
EC NO: 662617	2021/05/02																																										
DRWN: SBS04	2021/05/10																																										
CHK'D: MNARAYAN01	2021/05/10																																										
APPR: MNARAYAN01	2021/05/10																																										
DIVISIONAL SYMBOLS	<table border="1"> <tr> <th colspan="4">INITIAL REVISION:</th> </tr> <tr> <td>DRWN: SBS04</td> <td>2021/05/01</td> <td>DOCUMENT NUMBER</td> <td>DOC TYPE</td> </tr> <tr> <td>APPR: MNARAYAN01</td> <td>2021/05/10</td> <td>2171590205</td> <td>PSD</td> </tr> </table>	INITIAL REVISION:				DRWN: SBS04	2021/05/01	DOCUMENT NUMBER	DOC TYPE	APPR: MNARAYAN01	2021/05/10	2171590205	PSD	<table border="1"> <tr> <td>DOC PART</td> <td>REVISION</td> </tr> <tr> <td>000</td> <td>B</td> </tr> </table>	DOC PART	REVISION	000	B																									
INITIAL REVISION:																																											
DRWN: SBS04	2021/05/01	DOCUMENT NUMBER	DOC TYPE																																								
APPR: MNARAYAN01	2021/05/10	2171590205	PSD																																								
DOC PART	REVISION																																										
000	B																																										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER																																				
			A3-SIZE	217159	SEE TABLE	GENERAL MARKET	1 OF 1																																				