

Manual scissor-type lifting carriage

Load-bearing capacity 1000 kg with additional steering drawbar

fetra
Transportgeräte

Execution:

- Frame and forks in a stable, torsion-free section steel construction
- Strong tubular push handle
- Hydraulic pump with chrome-plated pistons and overload valve
- Operation via foot pedal
- Lowering valve activated via hand lever
- 2 castors, wheels, polyurethane tyres
- 150 x 40 mm and 2 fork rollers
- Nylon 70 x 65 mm, castors with locking device.
- with an additional steering drawbar

Advantage:

- Good stability, can be moved even when the load is lifted.



| | |
|---------------------------------|------------------|
| Art. no. | 50262 454 |
| Brand | FETRA |
| Manufacturer Part Number | 6821 |
| Load-carrying capacity | 1000 kg |
| Length | 1640 mm |
| Width | 687 mm |
| Fork length | 1115 mm |
| Fork arm width | 153 mm |
| Fork roller width | 65 mm |
| Fork roller diameter | 70 mm |
| Fork, external distance | 526 mm |
| Min. lift height | 85 mm |
| Lift height | 830 mm |
| Material of fork castor | Nylon |
| Material of wheel | Polyurethane |
| Wheel width | 40 mm |
| Wheel diameter | 150 mm |
| Total stop optional | No |
| Gross Weight | 135.000 kg |
| Product Group | 5AE |

EAN

4017976068213