



**ELECTRONICS, INC.**  
 44 FARRAND STREET  
 BLOOMFIELD, NJ 07003  
 (973) 748-5089

## NTE373 (NPN) & NTE374 (PNP) Silicon Complementary Transistors Audio Amplifier, Driver

**Absolute Maximum Ratings:** ( $T_A = +25^\circ\text{C}$  unless otherwise specified)

Collector–Base Voltage, $V_{CBO}$ .....	180V
Collector–Emitter Voltage, $V_{CEO}$ .....	160V
Emitter–Base Voltage, $V_{EBO}$ .....	5V
Collector Current, $I_C$	
Continuous .....	1.5A
Peak .....	3A
Collector Power Dissipation, $P_D$	
$T_A = +25^\circ\text{C}$ .....	1W
$T_C = +25^\circ\text{C}$ .....	20W
Operating Junction Temperature, $T_J$ .....	$+150^\circ\text{C}$
Storage Temperature Range, $T_{stg}$ .....	$-55^\circ$ to $+150^\circ\text{C}$

**Electrical Characteristics:** ( $T_A = +25^\circ\text{C}$  unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Collector–Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C = 1\text{mA}, I_E = 0$	180	–	–	V
Collector–Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = 10\text{mA}, R_{BE} = \infty$	160	–	–	V
Emitter–Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E = 1\text{mA}, I_C = 0$	5	–	–	V
Collector Cutoff Current	$I_{CBO}$	$V_{CB} = 160\text{V}, I_E = 0$	–	–	10	$\mu\text{A}$
DC Current Gain	$h_{FE1}$	$V_{CE} = 5\text{V}, I_C = 150\text{mA}$	60	–	200	
	$h_{FE2}$	$V_{CE} = 5\text{V}, I_C = 500\text{mA}$	30	–	–	
Collector–Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 500\text{mA}, I_B = 50\text{mA}$	–	–	1	V
Base–Emitter Voltage	$V_{BE}$	$V_{CE} = 5\text{V}, I_C = 150\text{mA}$	–	–	1.5	V
Transistion Frequency	$f_T$	$V_{CE} = 5\text{V}, I_C = 500\text{mA}$	–	140	–	MHz
Collector Output Capacitance	$C_{ob}$	$V_{CB} = 10\text{V}, I_E = 0, f = 1\text{MHz}$	–	14	–	pF

