

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Multi-channel electronic device circuit breaker for protecting four loads at 24 V DC in the event of overload and short circuit. With electronic locking of the set nominal currents. For installation on DIN rails.

Why buy this product

- Easy device replacement without replanning, thanks to compact design and options for individual adjustments
- ☑ Circuits can be adjusted without any tools by means of one single pushable LED button
- Reliable protection against unintentional adjustment of current values, thanks to electronic locking
- Status LEDs in traffic light colors enable instantaneous determination of operating states



Key Commercial Data

Packing unit	1 STK
GTIN	4 055626 149356
GTIN	4055626149356
Weight per Piece (excluding packing)	135.700 g
Custom tariff number	85363090
Country of origin	Germany

Technical data

Dimensions

Height	90 mm
Width	36 mm
Depth	98 mm

Ambient conditions

Ambient temperature (operation)	-25 °C 60 °C
Ambient temperature (storage/transport)	-40 °C 70 °C
Humidity test	96 h, 95% RH, 40°C
Altitude	2000 m
Degree of protection	IP20



Technical data

General

Flammability rating according to UL 94	V-0
Mounting type	DIN rail: 35 mm
Color	light grey RAL 7035
Protection class	III
Degree of pollution	2
Туре	DIN rail module, one-piece

Electrical data

Fuse type	electronic
Rated surge voltage	0.5 kV
Operating voltage	18 V DC 30 V DC
Rated voltage	24 V DC
Rated current I _N	max. 40 A DC
	max. 40 A DC (per terminal position when bridging additional devices via IN+)
	1 / 2 / 3 / 4 / 5 / 6 / 7 / 8 / 9 / 10 A DC (adjustable per output channel)
Measuring tolerance I	typ. 15 %
Rated insulation voltage U _i	30 V (Load circuit)
Feedback resistance	max. 35 V DC
Switch-on delay	0.1 s (Cascaded per output channel)
Required backup fuse	not required, integrated failsafe element
Internal output fuse	15 A DC (per output channel)
Status display	LED (green, yellow, red)
Efficiency	> 99 %
Closed circuit current I ₀	typ. 33 mA
Power dissipation	typ. 0.8 W (No-load operation)
	9 W (Nominal operation)
Module initialization time	1.6 s
Waiting time after switch off of a channel	5 s (of overload / short circuit)
Temperature derating	24 A DC (at 60°C)
	28 A DC (at 54°C)
	32 A DC (At 47°C)
	36 A DC (at 41°C)
	40 A DC (at 35°C)
Dielectric strength	max. 35 V DC (Load circuit)
Contact type	without electrical isolation
MTBF (IEC 61709, SN 29500)	8403361 h (at 25°C with 21% load)
	3067484 h (at 40°C with 34.25% load)
	534188 h (at 60°C with 100% load)
Shutdown time load circuit	\leq 10 ms (for short circuit > 2.0 x I _N)
	1 s (1.2 2.0 x I _N)



Technical data

Electrical data

Undervoltage shutdown load circuit	≤ 17.8 V DC (active)
	≥ 18.8 V DC (inactive)
Surge voltage shutdown load circuit	≥ 30.5 V DC (active)
	≤ 29.5 V DC (inactive)
Max. capacitive load load circuit	$45000\ \mu F$ (Depending on the current setting and the short-circuit current available)
Vibration resistance, frequency	10 Hz 150 Hz (58 Hz transmission frequency)
Vibration resistance, acceleration	49 m/s ²
Vibration resistance, test duration	150 min. (Per axis and direction)

Remote indication contact

Connection name	Remote indication circuit
Switching function	N/O contact
Stripping length	10 mm
Conductor cross section solid	0.2 mm² 2.5 mm²
Conductor cross section AWG	24 12
Conductor cross section, flexible, with ferrule, with plastic sleeve	0.25 mm² 1.5 mm²
Conductor cross section flexible, with ferrule without plastic sleeve	0.25 mm² 2.5 mm²
DC operating voltage	0 V DC 30 V DC
DC operating current	100 mA DC

Connection data

Connection name	Main circuit IN+
Connection method	Push-in connection
Stripping length	15 mm
Conductor cross section solid	0.2 mm² 10 mm²
Conductor cross section AWG	15 8
Conductor cross section, flexible, with ferrule, with plastic sleeve	0.25 mm² 4 mm²
Conductor cross section flexible, with ferrule without plastic sleeve	0.25 mm² 6 mm²
Connection name	Main circuit IN-
Connection method	Push-in connection
Stripping length	10 mm
Conductor cross section solid	0.2 mm² 2.5 mm²
Conductor cross section AWG	24 12
Conductor cross section, flexible, with ferrule, with plastic sleeve	0.25 mm² 1.5 mm²
Conductor cross section flexible, with ferrule without plastic sleeve	0.25 mm² 2.5 mm²
Connection name	Main circuit OUT
Connection method	Push-in connection
Stripping length	10 mm
Conductor cross section solid	0.2 mm² 2.5 mm²
Conductor cross section AWG	24 12
Conductor cross section, flexible, with ferrule, with plastic sleeve	0.25 mm² 1.5 mm²



Technical data

Connection data


Conductor cross section flexible, with ferrule without plastic sleeve	0.25 mm² 2.5 mm²
---	------------------

Standards and Regulations


Standards/specifications	EN 61000-6-2
	EN 61000-6-3
	EN 60068-2-78
	UL 508
	UL 2367

Drawings






Diagram




Trigger characteristic in the DC range


Dimensional drawing



Product drawing







Classifications

eCl@ss

eCl@ss 5.1	27141116
eCl@ss 6.0	27141116
eCl@ss 8.0	27141116
eCl@ss 9.0	27141116

ETIM

ETIM 5.0	EC000899
ETIM 6.0	EC000899

UNSPSC

UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

EAC / UL Listed / cUL Listed / UL Recognized / cULus Listed



Approvals

Ex Approvals

Approval details

EAC [H[

RU C-DE.A*30.B01561

UL Listed



http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

FILE E 123528

cUL Listed



http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

FILE E 123528

UL Recognized



http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

FILE E 317172

cULus Listed



Accessories

Additional products

Label - EML (10X7)R - 0816663



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK S1.1, Mounting type: adhesive, Lettering field: 10 x 7 mm

Equipment marking - EML-ESD (20X7)R - 0830567



Equipment marking, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK S1.1, Mounting type: adhesive, Lettering field: 20 x 7 mm



Accessories

Power supply unit - QUINT4-PS/1AC/24DC/10 - 2904601



Primary-switched QUINT POWER power supply with free choice of output characteristic curve, SFB (selective fuse breaking) technology, and NFC interface, input: 1-phase, output: 24 V DC/10 A

Power supply unit - QUINT4-PS/1AC/24DC/20 - 2904602



Primary-switched QUINT POWER power supply with free choice of output characteristic curve, SFB (selective fuse breaking) technology, and NFC interface, input: 1-phase, output: 24 V DC/20 A

Power supply unit - QUINT4-PS/3AC/24DC/10 - 2904621



Primary-switched QUINT POWER power supply with free choice of output characteristic curve, SFB (selective fuse breaking) technology, and NFC interface, input: 3-phase, output: 24 V DC/10 A

Power supply unit - QUINT4-PS/3AC/24DC/20 - 2904622



Primary-switched QUINT POWER power supply with free choice of output characteristic curve, SFB (selective fuse breaking) technology, and NFC interface, input: 3-phase, output: 24 V DC/20 A

Power supply unit - TRIO-PS-2G/1AC/24DC/10 - 2903149



Primary-switched TRIO POWER power supply with push-in connection for DIN rail mounting, input: single phase, output: 24 V DC/10 A



Accessories

Power supply unit - TRIO-PS-2G/1AC/24DC/20 - 2903151



Primary-switched TRIO POWER power supply with push-in connection for DIN rail mounting, input: single-phase, output: 24 V DC/20 A

Power supply unit - TRIO-PS-2G/3AC/24DC/5 - 2903153



Primary-switched TRIO POWER power supply with push-in connection for DIN rail mounting, input: 3-phase, output: 24 V DC/5 A

Power supply unit - TRIO-PS-2G/3AC/24DC/10 - 2903154



Primary-switched TRIO POWER power supply with push-in connection for DIN rail mounting, input: 3-phase, output: 24 V DC/10 A

Power supply unit - TRIO-PS-2G/3AC/24DC/20 - 2903155



Primary-switched TRIO POWER power supply with push-in connection for DIN rail mounting, input: 3-phase, output: 24 V DC/20 A

Power supply unit - TRIO-PS-2G/3AC/24DC/40 - 2903156



Primary-switched TRIO power supply for DIN rail mounting, input: 3-phase, output: 24 V DC/40 A, dynamic boost, tool-free fast connection technology for solid and stranded conductors with ferrule

Phoenix Contact 2017 © - all rights reserved http://www.phoenixcontact.com