

**Twist drill set, type N HSS with offset shank**  
for universal use up to 1000 N/mm<sup>2</sup>



**Application**

Standard geometry for universal use up to a strength of 1000 N/mm<sup>2</sup>.

**Version**

- Twist drill with universal standard geometry

**Advantage**

- excellent all-round properties and precise cutting pattern
- Steam treatment ensures favourable adherence of coolant
- Diameter-independent straight shank of uniform length for clamping and tooling advantages



Application	Steel (N/mm <sup>2</sup> )			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	30	20	10	10	8	40	60	50	30	30	20	20	10	20	4				

<b>Art. No.</b>	<b>11067 900</b>
<b>Composition of set</b>	Ø 13.5-20 mm
<b>Pitch of drill diameter</b>	0.5 mm
<b>Number of pieces in assortment/set</b>	14 PCS

**EAN-Code**

4050293033595