

## Screw tap, HSSE M ISO 2 (6H) 0° 371 B

For use in stainless steels

**ATORN®**



### Application

For producing metric threads on CNC or conventional machines in **through holes** in the stainless steel material group.

### Version

- Dimensions to: DIN 371 = reinforced shank (to M10), DIN 376 = protruding shank (from M12)

### Advantage

- Long service life and process reliability through innovative cutting geometry in machining stainless steel

| Application | Steel (N/mm <sup>2</sup> ) |       |       | Stainless steel |         | Alu   |      | Brass |      | Bronze |      | Plas-tics | Graphite G(C)FK | GG(G) GjMW | Titan-alloy | Nickel-alloy | Super-alloy | Hard mat. |         |
|-------------|----------------------------|-------|-------|-----------------|---------|-------|------|-------|------|--------|------|-----------|-----------------|------------|-------------|--------------|-------------|-----------|---------|
|             | <700                       | <1000 | <1300 | marten.         | austen. | short | long | short | long | short  | long |           |                 |            |             |              |             | <55 HRC   | <65 HRC |
|             | 16                         | 12    |       | 9               | 10      |       |      |       |      |        |      |           |                 |            |             |              |             |           |         |

|   |                      |
|---|----------------------|
| <b>Art. No.</b>                               | <b>13136 100</b>     |
| <b>Type</b>                                   | M MAX Control        |
| <b>Thread type</b>                            | Metric thread        |
| <b>Thread type x nominal diameter</b>         | M10                  |
| <b>Pitch</b>                                  | 1.5 mm               |
| <b>Hole type</b>                              | Clearance hole ≤ 3xD |
| <b>Cutting material</b>                       | HSSE                 |
| <b>Surface</b>                                | Vaporised            |
| <b>Lead angle shape</b>                       | B                    |
| <b>Tolerance of screw taps</b>                | ISO 2 (6H)           |
| <b>Twist angle</b>                            | 0°                   |
| <b>Shaft diameter</b>                         | 10 mm                |
| <b>Application type/machine type</b>          | CNC, Conventional    |
| <b>Core hole diameter</b>                     | 8.5 mm               |
| <b>Coolant supply</b>                         | External             |
| <b>Length</b>                                 | 100 mm               |
| <b>Shank square</b>                           | 8 mm                 |
| <b>Cutting speed (steel 1000) suitability</b> | 2                    |
| <b>Cutting speed (steel 1300) suitability</b> | 3                    |
| <b>Overall stainless steel suitability</b>    | 1                    |
| <b>fitness not iron total</b>                 | 3                    |
| <b>fitness Titan/Nickel/Super total</b>       | 3                    |
| <b>Cutting speed (cast) suitability</b>       | 3                    |
| <b>Cutting speed (hard 55) suitability</b>    | 3                    |
| <b>Cutting speed (hard 65) suitability</b>    | 3                    |
| <b>DIN</b>                                    | 371                  |

### EAN-Code

4050293040531