

CKUN steel boring bar, negative, left

for longitudinal turning with KN indexable insert

ATORN[®]

Application

For longitudinal turning using KN 55° indexable insert.

Version

- precision-manufactured steel boring bar, K type, 93° pitch angle, 55° tip angle, 0° clearance angle

Advantage

- optimised geometry for low-performance machines
- positive cutting geometry of the indexable insert ensures low cutting forces
- wide range of delivery: suitable for both finishing and roughing



Art. No.	17851 016
ISO name	S 32 U CKUN R/L 16
Min. bore diameter	39 mm
Shaft diameter	32 mm
Clearance length	54 mm
Length	350 mm
Clamping surface height	30 mm
Programming size	22 mm
Suitable for indexable inserts	KNUX 1604..
Tool design	Left
DIN	8024

EAN-Code

4050293127539