

Fully extending drawer for HK cabinet/shelving system 550

Depth 450 mm

Application:

For individual configuration of the HK cabinet housing/tool shelves. The drawers can be installed in the housing in any sequence, but the sum of the front heights must be equal to the useful height of the housing.

Execution:

- Made of sheet steel with a reinforced, perforated bottom (25 mm hole grid)
- Run on Delrin rollers in rails which are suspended in the housing with plug caps
- Inner sides slotted all around, for attaching and fixing insert material such as compartment rails and dividers
- Equipped with aluminium handle strip, paper and cellon strips and lateral cover caps
- SOFT-CLOSE-AUTOMATIC for smooth and silent drawer closing, see no. 50392 005.



Art. no.	50295 279
Brand	HK
Manufacturer Part Number	50295279
Drawer front height	60 mm
Suitable for system	550 S
Drawer cabinet height	40 mm
Mount height	40 mm
Drawer width (inner dimension)	600 mm
Drawer depth (inner dimension)	450 mm
Drawer surface	0.27 m ²
Pullout type	Full extension
Load-carrying capacity	70 kg
Drawer with slots	Yes
Perforated drawer base	Yes
Material	Sheet steel
Colour of front	Anthracite grey RAL 7016
Box colour	Light grey RAL 7035
Surface	Powder-coated
Gross Weight	8.000 kg
Product Group	5BB

EAN

4053625403486