

6EH8 ✓ ACTIVE

[Corcom](#) | [Corcom H](#)

TE Internal #: 6609013-3

Corcom H, Single Phase Filters, 6A Filter Current Rating, Flanged, IEC Input, Wire Lead Output, Leakage Current (Max) (120VAC, 60Hz) .002 mA

[View on TE.com >](#)



[EMI Filters](#) > [Power Line Filters](#) > [Single Phase Filters](#) > [CORCOM H SERIES SINGLE PHASE FILTERS](#)



Filter Current Rating: **6 A**

Filter Mount Style: **Flanged**

Filter Input Termination Type: **IEC**

Filter Output Termination Type: **Wire Lead**

Leakage Current (Max) (120VAC, 60Hz): **.002 mA**

[All CORCOM H SERIES SINGLE PHASE FILTERS \(15\)](#)

## Features

### Product Type Features

Ground Choke Option	No
Filter Type	Power Line
Filtering Requirements	Filtered
Filter Input Termination Type	IEC
Filter Output Termination Type	Wire Lead

### Electrical Characteristics

Voltage (Max)	250 VAC
Filter Current Rating	6 A
Leakage Current (Max) (120VAC, 60Hz)	.002 mA
Leakage Current (Max) (250VAC, 50Hz)	.005 mA

### Mechanical Attachment

Filter Mount Style	Flanged
--------------------	---------

### Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




## Also in the Series | Corcom H



Single Phase Filters(15)

## Customers Also Bought



TE Part #1470364-4  
AMP HPI 1.0MM RECEPTACLE  
HOUSINGS



TE Part #1-480393-1  
02P CMNL PLUG HSG F/H BLK



TE Part #1-440146-2  
1.25mm WTB Socket,Housing,12p



TE Part #1-534237-3  
15 MODII VRT SR CE 100/115



TE Part #1734327-1  
MINI USB, TYPE A, R/A, SMT



TE Part #1-480401-0  
01P CMNL CAP HSG F/H BLK



TE Part #1693800-1  
CURING FIXT, BULK



TE Part #1484225-1  
FILLER PLUG, SIZE 5



TE Part #1-2364570-9  
AVH19 FLT SS MT RNG BLU 24V16A



TE Part #ZPF000000000019178  
FDPA 56-12-10 SZ-K-A5357

## Documents

### Product Drawings

[6EH8=F7567 S0](#)

English

### CAD Files

[Customer View Model](#)

[ENG\\_CVM\\_6609013-3\\_1.3d\\_igs.zip](#)

English

[Customer View Model](#)



[ENG\\_CVM\\_6609013-3\\_1.3d\\_stp.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_6609013-3\\_1.2d\\_dxf.zip](#)

English

**3D PDF**

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[1654001\\_CORCOM\\_PRODUCT\\_GUIDE\\_H\\_SERIES](#)

English

[1654001\\_CORCOM\\_PRODUCT\\_GUIDE](#)

English

[Corcom Combined Selector Charts](#)

English