- Fastenings at angles up to 30° per side
- Quick feeding of the key into the screw thanks to feeding from various angles
- The key does not slip out of the screw, which reduces the risk of accidents
- No deformation of the screw head thanks to precision fitting of the ball end
- Fastenings at angles up to 25° per side
- Higher torque transmission due to maximum core diameter
- Elongated profile positioning for further use of the L-key
- Thanks to the combination of MagicRing® with the Wiha ball end, inserting and removing screws is possible, even in hard-to-reach locations
- Securely holds screws made of steel and non-magnetic materials such as stainless steel, titanium, aluminium and plastics in any position
- Can be used for all standard screws
- Use for applications in which magnetised fastening tools cannot and may not be used (magnetic environment)!
- Fastenings at angles up to 25° per side
- Securely holds screws made of steel and non-magnetic materials such as stainless steel, titanium, aluminium and plastics in any position
- TORX® and TORX PLUS® screws manufactured according to Camcar Textron specifications
- Use for applications in which magnetised fastening tools cannot and may not be used (magnetic environment)!
- Reduction of the short L-key arm, especially for hard-to-reach screws
- Increase in the hand working space of over 30% and thus a reduction of the risk of injury to the knuckles and fingertips thanks to a 95° bend of the L-key
- Improved access through a reduction of the L-key head height of up to 15%
- \bullet Ball end geometry enables fastening at an angle of up to 25°
- Handles and holders in the same colour depending on the output size
- This provides an overview of the tool assortment



Wiha hexagon L-key (metric).

For Allen screws (metric).



369F Ball end hex L-key, long.

Blade: Chrome vanadium steel, through-hardened, colour-coded.

Standards: Based on ISO 2936L.

Application: Especially for screws that are difficult to access.

Extra: The ball end enables the user to work at angles up to 25°.

Colour coding for immediate identification of L-keys.

Order-No.	•			∢Œ	
34269	1.5	91	15	black	10
34270	2	101	18	green	10
34271	2.5	113	20	turquoise	10
34272	3	128	23	light blue	10
34273	4	142	29	purple	10
34274	5	163	33	red	10
34275	6	184	38	orange	10
34276	8	206	44	yellow	10
34277	10	231	50	grey	5

95°

369T S9

Extra:

Ball end hex L-key set in ProStar.

Chrome-plated, 9 pcs.

Blade: Chrome-vanadium steel, through hardened, chrome-plated.

Standards: Based on ISO 2936L.

Application: Specially for hard-to-reach screws and confined spaces.

Space saving ProStar allows the easy removal of each key without

moving any others.


Increase in the hand working space of over 30% and thus a reduction of risk of injury to the knuckles and fingertips thanks to 95° bend of the L-key. Improved access through a reduction of the L-key head height of

up to 15%.

The ball end enables the user to work at angles up to 25°.

Order-No.	Series						
35480	369T S9						5
•	369T	1.5	2	2.5	3	4	

For Allen screws (metric).



369T Ball end hex L-key, long.

Blade: Chrome-vanadium steel, through hardened, chrome-plated.

Standards: Based on ISO 2936L.

Application: Specially for hard-to-reach screws and confined spaces.

Extra: Increase in the hand working space of over 30% and thus a reduction of risk of injury to the knuckles and fingertips thanks to 95° bend of the L-key. Improved access through a reduction of the L-key head height of

up to 15%

The ball end enables the user to work at angles up to 25°.

Order-No.	•		ţ	
35482	1.5	91	5.5	10
35483	2	101	9	10
35484	2.5	113	9.5	10
35485	3	128	11	10
35486	4	142	13	10
35487	5	163	15	10
35488	6	184	18	10
35489	8	206	22	10