

BSH1002P31A2A

AC servo motor BSH - 3.4 N.m - 2500 rpm -
keyed shaft - without brake - IP65





Main

Product or component type	Servo motor
Device short name	BSH
Maximum mechanical speed	6000 rpm
Continuous stall torque	4.5 N.M for LXM15LD21M3, 230 V, single phase 3.4 N.M for LXM15LD13M3, 230 V, three phase 3.4 N.M for LXM15LD10N4, 230 V, three phase 3.4 N.M for LXM15LD10N4, 400 V, three phase 3.4 N.M for LXM15LD10N4, 480 V, three phase 5.8 N.M for LXM15LD17N4, 400 V, three phase 5.8 N.M for LXM15LD17N4, 480 V, three phase 5.8 N.M for LXM15LD21M3, 230 V, three phase 5.5 N.M for LXM05AD17M3X, 200...240 V, three phase 5.5 N.M for LXM05AD22N4, 380...480 V, three phase 5.5 N.M for LXM05AD28M2, 200...240 V, single phase 5.5 N.M for LXM05BD17M3X, 200...240 V, three phase 5.5 N.M for LXM05BD22N4, 380...480 V, three phase 5.5 N.M for LXM05BD28M2, 200...240 V, single phase 5.5 N.M for LXM05CD17M3X, 200...240 V, three phase 5.5 N.M for LXM05CD22N4, 380...480 V, three phase 5.5 N.M for LXM05CD28M2, 200...240 V, single phase 5.8 N.M for LXM32.D18N4 at 6 A, 400 V, three phase 5.8 N.M for LXM32.D18N4 at 6 A, 480 V, three phase
Peak stall torque	9.39 N.M for LXM15LD21M3, 230 V, single phase 5.6 N.M for LXM15LD13M3, 230 V, three phase 8 N.M for LXM15LD10N4, 230 V, three phase 8 N.M for LXM15LD10N4, 400 V, three phase 8 N.M for LXM15LD10N4, 480 V, three phase 12.13 N.M for LXM15LD17N4, 400 V, three phase 12.13 N.M for LXM15LD17N4, 480 V, three phase 14.79 N.M for LXM15LD21M3, 230 V, three phase 11.23 N.M for LXM05AD17M3X, 200...240 V, three phase 13.92 N.M for LXM05AD22N4, 380...480 V, three phase 16 N.M for LXM05AD28M2, 200...240 V, single phase 11.23 N.M for LXM05BD17M3X, 200...240 V, three phase 13.92 N.M for LXM05BD22N4, 380...480 V, three phase 16 N.M for LXM05BD28M2, 200...240 V, single phase 11.23 N.M for LXM05CD17M3X, 200...240 V, three phase 13.92 N.M for LXM05CD22N4, 380...480 V, three phase 16 N.M for LXM05CD28M2, 200...240 V, single phase 18.3 N.M for LXM32.D18N4 at 6 A, 400 V, three phase 18.3 N.M for LXM32.D18N4 at 6 A, 480 V, three phase

Nominal output power	<p>950 W for LXM15LD21M3, 230 V, single phase</p> <p>950 W for LXM15LD21M3, 230 V, three phase</p> <p>780 W for LXM05AD28M2, 200...240 V, single phase</p> <p>780 W for LXM05BD28M2, 200...240 V, single phase</p> <p>780 W for LXM05CD28M2, 200...240 V, single phase</p> <p>1400 W for LXM05AD22N4, 380...480 V, three phase</p> <p>1400 W for LXM05BD22N4, 380...480 V, three phase</p> <p>1400 W for LXM05CD22N4, 380...480 V, three phase</p> <p>1600 W for LXM15LD10N4, 400 V, three phase</p> <p>1700 W for LXM15LD17N4, 400 V, three phase</p> <p>1950 W for LXM15LD17N4, 480 V, three phase</p> <p>2150 W for LXM15LD10N4, 480 V, three phase</p> <p>780 W for LXM05AD17M3X, 200...240 V, three phase</p> <p>780 W for LXM05BD17M3X, 200...240 V, three phase</p> <p>780 W for LXM05CD17M3X, 200...240 V, three phase</p> <p>840 W for LXM15LD13M3, 230 V, three phase</p> <p>890 W for LXM15LD10N4, 230 V, three phase</p> <p>1700 W for LXM32.D18N4 at 6 A, 400 V, three phase</p> <p>1700 W for LXM32.D18N4 at 6 A, 480 V, three phase</p>
Nominal torque	<p>4.5 N.M for LXM15LD21M3, 230 V, single phase</p> <p>4.96 N.M for LXM05AD28M2, 200...240 V, single phase</p> <p>4.96 N.M for LXM05BD28M2, 200...240 V, single phase</p> <p>4.96 N.M for LXM05CD28M2, 200...240 V, single phase</p> <p>3.4 N.M for LXM15LD10N4, 230 V, three phase</p> <p>3.4 N.M for LXM15LD10N4, 400 V, three phase</p> <p>3.4 N.M for LXM15LD10N4, 480 V, three phase</p> <p>3.4 N.M for LXM15LD13M3, 230 V, three phase</p> <p>3.7 N.M for LXM15LD17N4, 480 V, three phase</p> <p>4 N.M for LXM15LD17N4, 400 V, three phase</p> <p>4.4 N.M for LXM05AD22N4, 380...480 V, three phase</p> <p>4.4 N.M for LXM05BD22N4, 380...480 V, three phase</p> <p>4.4 N.M for LXM05CD22N4, 380...480 V, three phase</p> <p>4.96 N.M for LXM05AD17M3X, 200...240 V, three phase</p> <p>4.96 N.M for LXM05BD17M3X, 200...240 V, three phase</p> <p>4.96 N.M for LXM05CD17M3X, 200...240 V, three phase</p> <p>5.8 N.M for LXM15LD21M3, 230 V, three phase</p> <p>4 N.M for LXM32.D18N4 at 6 A, 400 V, three phase</p> <p>4 N.m for LXM32.D18N4 at 6 A, 480 V, three phase</p>

Nominal speed	3000 rpm for LXM05AD22N4, 380...480 V, three phase 3000 rpm for LXM05BD22N4, 380...480 V, three phase 3000 rpm for LXM05CD22N4, 380...480 V, three phase 1500 rpm for LXM05AD17M3X, 200...240 V, three phase 1500 rpm for LXM05BD17M3X, 200...240 V, three phase 1500 rpm for LXM05CD17M3X, 200...240 V, three phase 4500 rpm for LXM15LD10N4, 400 V, three phase 6000 rpm for LXM15LD10N4, 480 V, three phase 4000 rpm for LXM32.D18N4 at 6 A, 400 V, three phase 4000 rpm for LXM32.D18N4 at 6 A, 480 V, three phase 1500 rpm for LXM05AD28M2, 200...240 V, single phase 1500 rpm for LXM05BD28M2, 200...240 V, single phase 1500 rpm for LXM05CD28M2, 200...240 V, single phase 2000 rpm for LXM15LD21M3, 230 V, single phase 2000 rpm for LXM15LD21M3, 230 V, three phase 2500 rpm for LXM15LD10N4, 230 V, three phase 2500 rpm for LXM15LD13M3, 230 V, three phase 4000 rpm for LXM15LD17N4, 400 V, three phase 5000 rpm for LXM15LD17N4, 480 V, three phase
Product compatibility	LXM05AD28M2 at 200...240 V single phase LXM05BD28M2 at 200...240 V single phase LXM05CD28M2 at 200...240 V single phase LXM15LD21M3 at 230 V single phase LXM15LD13M3 at 230 V three phase LXM15LD10N4 at 400 V three phase LXM05AD17M3X at 200...240 V three phase LXM05BD17M3X at 200...240 V three phase LXM05CD17M3X at 200...240 V three phase LXM15LD10N4 at 230 V three phase LXM15LD10N4 at 480 V three phase LXM15LD21M3 at 230 V three phase LXM05AD22N4 at 380...480 V three phase LXM05BD22N4 at 380...480 V three phase LXM05CD22N4 at 380...480 V three phase LXM15LD17N4 at 400 V three phase LXM15LD17N4 at 480 V three phase LXM32.D18N4 at 400 V three phase LXM32.D18N4 at 480 V three phase
Shaft end	Keyed
IP degree of protection	IP65 standard IP67 with IP67 kit
Speed feedback resolution	131072 points/turn
Holding brake	Without
Mounting support	International standard flange
Electrical connection	Rotatable right-angled connectors

Complementary

Range compatibility	Lexium 32 Lexium 15 Lexium 05
Supply voltage max	480 V
Network number of phases	Three phase
Continuous stall current	4.8 A
Maximum continuous power	2.51 W

Maximum current Irms	17.1 A for LXM15LD13M3 17.1 A for LXM15LD21M3 17.1 A for LXM15LD10N4 17.1 A for LXM15LD17N4 17.1 A for LXM05AD28M2 17.1 A for LXM05AD17M3X 17.1 A for LXM05AD22N4 17.1 A for LXM05BD28M2 17.1 A for LXM05BD17M3X 17.1 A for LXM05BD22N4 17.1 A for LXM05CD28M2 17.1 A for LXM05CD17M3X 17.1 A for LXM05CD22N4 17.1 A for LXM32.D18N4
Maximum permanent current	17.1 A
Switching frequency	8 kHz
Second shaft	Without second shaft end
Shaft diameter	19 mm
Shaft length	40 mm
Key width	30 mm
Feedback type	Single turn SinCos Hiperface
Motor flange size	100 mm
Number of motor stacks	2
Torque constant	1.21 N.m/A at 120 °C
Back emf constant	77 V/krpm at 120 °C
Number of motor poles	8
Rotor inertia	2.31 kg.cm ²
Stator resistance	2.4 Ohm at 20 °C
Stator inductance	12.7 mH at 20 °C
Stator electrical time constant	5.29 ms at 20 °C
Maximum radial force Fr	620 N at 4000 rpm 690 N at 3000 rpm 790 N at 2000 rpm 990 N at 1000 rpm
Maximum axial force Fa	0.2 x Fr
Type of cooling	Natural convection
Length	204.5 mm
Centring collar diameter	95 mm
Centring collar depth	3.5 mm
Number of mounting holes	4
Mounting holes diameter	9 mm
Circle diameter of the mounting holes	115 mm
Net weight	5.9 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	6.878 kg
Package 1 Height	20.0 cm
Package 1 width	22.0 cm
Package 1 Length	40.0 cm
Unit Type of Package 2	P06
Number of Units in Package 2	12
Package 2 Weight	91.036 kg
Package 2 Height	77.0 cm
Package 2 width	80.0 cm
Package 2 Length	60.0 cm

Offer Sustainability


Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) M4 screw
- (2) Shaft end, keyed slot (optional)

Dimensions in mm

Straight connectors		Rotatable angled connectors		c (without brake)	c (with brake)	c1	c2	h	h1	Ø	Ø1 for screws
b1	b2	b1	b2								
39.5	25.5	39.5	39.5	205	236	40	30	6 N9	3.5 ^{+0.1} ₀	19 k6	M6 x 16


Dimensions in in.

Straight connectors		Rotatable angled connectors		c (without brake)	c (with brake)	c1	c2	h	h1	Ø	Ø1 for screws
b1	b2	b1	b2								
1.55	1.00	1.55	1.55	8.07	9.29	1.57	1.18	0.24 N9	0.14 ^{+0.1} ₀	0.75 k6	M6 x 0.63

400 V 3-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D18N4 servo drive



X Speed in rpm

Y Torque in Nm


1 Peak torque

2 Continuous torque

480 V 3-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D18N4 servo drive



X Speed in rpm

Y Torque in Nm

1 Peak torque

2 Continuous torque