

Axial Vitreous Wirewound Resistors



FEATURES

- Complete welded construction
- Vitreous coating
- Enhanced humidity protection
- TCR 100...180 ppm/K
- Pure tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes
- Compatible with "Restriction of the use of Hazardous Substances" (RoHS) directive 2002/95/EC (issue 2004)



STANDARD ELECTRICAL SPECIFICATIONS						
GLOBAL MODEL	HISTORICAL MODEL	APPROVED	POWER RATING $P_{40^\circ\text{C}}$ W	RESISTANCE RANGE E12/E24		LIMITING VOLTAGE V
		CECC 40201-801		TOL. $\pm\%$	Ω	
G220414	G202	FDG	4	10 5 2 1	R10 - 10K R10 - 10K R36 - 10K ⁽¹⁾ on request	200
G240719	G204	FDK	7	10 5 2 1	R10 - 39K R10 - 39K R10 - 39K on request	350
G260933	G206	FDP	13	10 5 2 1	R15 - 68K R15 - 68K R15 - 68K on request	500
G270947	G207		17	10 5 2 1	R20 - 120K R20 - 120K R20 - 120K on request	650


Note

⁽¹⁾ R10 - R36 on request

GLOBAL PART NUMBER INFORMATION																	
New Global Part Numbering: G24071933902J4B000 (preferred part number format)																	
G	2	4	0	7	1	9	3	3	9	0	2	J	4	B	0	0	0
MODEL (See Standard Electrical Specifications table)	TCR/MATERIAL 3 = Class 3 WM110 100...180 ppm/K		VALUE 3 digit value 1 digit multiplier 7 = *10 ⁻³ 8 = *10 ⁻² 9 = *10 ⁻¹ 0 = *10 ⁰ 1 = *10 ¹ 2 = *10 ² 3 = *10 ³			TOLERANCE F = $\pm 1.0\%$ G = $\pm 2.0\%$ J = $\pm 5.0\%$ K = $\pm 10.0\%$		PACKAGING (See Packaging table)		SPECIAL The 5 digit BV number will be encoded using a 36 character code. This code contains numbers 0...9 and letters A...Z (36 characters total) and allows to encode at least 46 655 five digit BV numbers. 000 = Standard							
Historical Part Number Example: G204 39K 5% AB G73 (will continue to be accepted)																	
G204		39K			5%		AB G73										
HISTORICAL MODEL		VALUE			TOLERANCE		PACKAGING										

PACKAGING TABLE			
SAP	DRALORIC LEGACY	DESCRIPTION	TYPE
2C	AC G53	Ammo pack tape 53 mm, 500 pieces	G202
4B	AB G73	Ammo pack tape 73 mm, 250 pieces	G204
4C	AC G73	Ammo pack tape 73 mm, 500 pieces	G202
7B	AB G88	Ammo pack tape 88 mm, 250 pieces	G204
8B	AB G88 CL	Ammo pack tape 88 mm, CL, 250 pieces	G204
D1	R1 G53	Reel pack tape 53 mm, 1000 pieces	G202
F1	R1 G73	Reel pack tape 73 mm, 1000 pieces	G202
FC	RC G73	Reel pack tape 73 mm, 500 pieces	G204
IC	RC G88	Reel pack tape 88 mm, 500 pieces	G204
LA	LA	loose pack, 100 pcs	G206, G207
LD	-	loose pack, 50 pieces	G204
LJ	-	loose pack, 200 pieces	G204
LL	-	loose pack, 400 pieces	-

DIMENSIONS








For packaging dimensions see separate packaging dimensions page.

MODEL	DIMENSIONS in millimeters [inches]				
	A _{max.}	B _{max.} ⁽¹⁾	C ⁽²⁾	D _{min.}	Weight (g)
G 202	13 [0.512]	5.7 [0.224]	0.8 [0.031]	53 ± 1 [2.087 ± 0.039]	1
G 204	19.3 [0.760]	8.5 [0.335]	0.8 [0.031]	73 ± 1 [2.874 ± 0.039]	2.2
G 206	32.3 [1.272]	9.8 [0.386]	0.8 [0.031]	107 ± 2 [4.213 ± 0.079]	6.5
G 207	49.3 [1.941]	10.5 [0.413]	0.8 [0.031]	120 ± 2 [4.724 ± 0.079]	10

Note

⁽¹⁾ The body diameter should be increased by 1 mm [0.039"] for ohmic values ≤ 10 Ω

⁽²⁾ C according to IEC60301





PERFORMANCE	
TEST	TEST RESULTS
Damp Heat, Steady State	$\pm 5 \% \Delta R$
Climatic Sequence	$\pm 5 \% \Delta R$
Load Life	$\pm 5 \% \Delta R$
Short Time Overload	$\pm 1 \% \Delta R$
Vibration	$\pm 1 \% \Delta R$
Shock	$\pm 1 \% \Delta R$
Resistance to Soldering Heat	$\pm 1 \% \Delta R$



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.