RoHS

Compliant



# **Description:**

The resistors are constructed in a high grade ceramic body (aluminum oxide). Internal metal electrodes are added at each end and connected by a resistive paste that is applied to the top surface of the substrate. The composition of the paste is adjusted to give the approximate resistance required and the value is trimmed to within tolerance by laser cutting of this resistive layer.

The resistive layer is covered with a protective coat. Finally, the two external end terminations are added. For ease of soldering the outer layer of these end terminations is a Tin (lead free) alloy.

### Features:

- · High reliability and stability
- Reduced size of final equipment •
- Lower assembly costs
- Higher component and equipment reliability

## Application:

- Consumer electrical equipment
- EDP, Computer application
- Telecom application

# **Quick Reference Data**

ltem	General Specification				
Series No.	MCWR12	MCWR08	MCWR06	MCWR04	
Size code	1206(3216)	0805(2012)	0603(1608)	0402(1005)	
Resistance Range	1Ω to10MΩ 1% tolerance				
Resistance Tolerance	1% E96/E24				
TCR (ppm/°C) 10MΩ ≥R >10 R≤10Ω	≤ ± 100 -200 to +400				
Max. dissipation @ T <sub>amb</sub> =70°C	1/4 W	1/10 W	1/16 W		
Max. Operation Voltage (DC or RMS)	200V	150V	75V	50V	
Max. Overload Voltage (DC or RMS)	400V	400V 300V 150V			
Climatic category	55/155/56				

### Note :


1. Max. Operation Voltage : So called RCWV (Rated Continuous Working Voltage) is determined by RCWV = \Rated Power × Resistance Value or Max. RCWV listed above, whichever is lower.

2. The resistance of Jumper is defined <  $0.05\Omega$ .



	MCWR12	MCWR08	MCWR06	MCWR04
L	3.1 ± 0.1	2 ± 0.1	1.6 ± 0.1	1 ± 0.05
W	1.6 ± 0.1	1.25 ± 0.1	0.8 ± 0.1	$0.50 \pm 0.05$
Т	0.6 ± 0.15	0.5 ± 0.15	0.45 ± 0.15	$0.35 \pm 0.05$
Tb	0.45 ± 0.2	0.4 ± 0.2	0.3 ± 0.15	0.25 ± 0.1
Tt	0.5 ± 0.2	0.4 ± 0.2	0.3 ± 0.1	0.2 ± 0.1

**Dimensions : Millimetres** 




# **Functional Description:**


### **Product characterization**

Standard values of nominal resistance is E96 series for resistors with a tolerance of ±1%.

#### Derating

The power that the resistor can dissipate depends on the operating temperature; see Fig.2





### Mounting

Due to their rectangular shapes and small tolerances, Surface Mountable Resistors are suitable for handling by automatic placement systems.

Chip placement can be on ceramic substrates and printed-circuit boards (PCBs).

Electrical connection to the circuit is by individual soldering condition.

The end terminations guarantee a reliable contact.



# **Soldering Condition:**

The robust construction of chip resistors allows them to be completely immersed in a solder bath of 260°C for 10 seconds. Therefore, it is possible to mount Surface Mount Resistors on one side of a PCB and other discrete components on the reverse (mixed PCBs).

Surface Mount Resistors are tested for solderability at 235°C during 2 seconds. The test condition for no leaching is 260°C for 30 seconds. Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 3.




Fig 3. Infrared soldering profile for Chip Resistors

## Catalogue Numbers:

The resistors have a catalogue number starting with

MCWR12	Х	472_	J	т	L
Size code	Type code	Resistance code	Tolerance	Packaging code	Termination
MCWR12 : 1206 MCWR08 : 0805 MCWR06 : 0603 MCWR04: 0402	<b>X</b> : ±1%, 10Ω to 1MΩ <b>W</b> : ±1%, < 10Ω; >1MΩ	$\pm 5\%, E24: 2 \text{ significant} digits followed by no. of zeros and a blank4.7\Omega = 4R7_{-} \\10\Omega = 100_{-} \\220\Omega = 221_{-} \\Jumper = 000_{-} \\("_" means a blank) \\\pm 1\%, E24+E96: 3 \text{ significant} \\digits followed by no. of zeros \\102\Omega = 1020 \\37.4K\Omega = 3742 \\$	F : ±1% P : Jumper	T : 7" Reeled taping Q : 10" Reeled taping G : 13" Reeled taping H : 13" reel 50Kpcs only for 0402 B : Bulk D : 7" reel 20Kpcs only for 0402 A : 7" reel 15Kpcs only for 0402	code L = Sn base (lead free)

MCWR12, MCWR08, MCWR06:

1. Reeled tape packaging : 8mm width paper taping 5,000pcs per 7" reel, 10kpcs per 10" reel, 20kpcs per 13" reel.

2. Bulk packaging : 5,000pcs per poly-bag

MCWR04:

1. Reeled tape packaging : 8mm width paper taping 10,000pcs per 7" reel, 20,000pcs per 10" reel. 70,000pcs per 13" reel.

2. Bulk packaging : 10,000pcs per poly-bag



## **Test and Requirements:**

Essentially all tests are carried out according to the schedule of IEC publication 115-8, category LCT/UCT/56 (rated temperature range : Lower Category Temperature, Upper Category Temperature; damp heat, long term, 56 days). The testing also meets the requirements specified by EIA, EIAJ and JIS.

The tests are carried out in accordance with IEC publication 68, "Recommended basic climatic and mechanical robustness testing procedure for electronic components" and under standard atmospheric conditions according to IEC 60068-1, subclause 5.3. Unless otherwise specified, the following value supplied :

Temperature: 15°C to 35°C.

Relative humidity: 45% to 75%.

Air pressure: 86kPa to 106 kPa (860 mbar to 1060 mbar).

All soldering tests are performed with midly activated flux.

Test	Procedure / Test Method	Requirement		
Test	Procedure / Test Method	Resistor	0Ω	
$ \begin{array}{c} - \text{ DC resistance values measurement} \\ - \text{ Temperature Coefficient of Resistance (T.C.R)} \\ \text{Natural resistance change per change in degree centigral} \\ \text{Characteristics} \\ \text{JISC5201-1: 1998} \\ \text{Clause 4.8} \end{array} \qquad \qquad \begin{array}{c} - \text{ DC resistance values measurement} \\ - \text{ Temperature Coefficient of Resistance (T.C.R)} \\ \text{Natural resistance change per change in degree centigral} \\ \frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (ppm/°C) } t_1 : 20^\circ \text{C} + 5^\circ \text{C} / -1^\circ \text{C}; t_2 : -55^\circ \text{C or} \\ R_1 : \text{ Resistance at reference temperature (20^\circ \text{C} + 5^\circ \text{C} / -1 \\ R_2 : \text{ Resistance at test temperature (-55^\circ \text{C or } +155^\circ \text{C})} \end{array} $		Within the specified tolerance Refer to "QUICK REFERENCE DATA"	<50mΩ	
Resistance to soldering heat(R.S.H) Un-mounted chips completely immersed for 10 ±1second in a		$\pm$ 1%: ΔR/Rmax. $\pm$ (0.5%+0.05Ω ) no visible damage	<50mΩ	
Solderability JISC5201-1: 1998 Clause 4.17	Un-mounted chips completely immersed for 10 ±1second in a SAC solder bath at 235°C ±5°C	95% coverage min., good tinning and no visible damage		
Temperature cycling JISC5201-1: 1998 Clause 4.19	JISC5201-1: 1998 JISC5200-1: 1998 JISC5		<50mΩ	
High TemperatureExposure1,000 +48/-0 hours; without load in a temperature chamberMIL-STD-202controlled 155 ±3°Cmethod 108method 108		±1%:∆R/ Rmax.±(1%+0.1Ω) No visible damage	<50mΩ	
Bending strength JISC5201-1: 1998 Clause 4.33 Resistors mounted on a 90mm glass epoxy resin PCB(FR4), bending once 3mm for 10sec, 5mm for MCWR04		$\pm$ 1%:ΔR/ Rmax. $\pm$ (1%+0.05Ω) No visual damaged	<50mΩ	
Adhesion JISC5201-1: 1998 Clause 4.32	C5201-1: 1998 Pressurizing force: 5N, Test time: 10 ±1sec.		e or ions	
Short Time Overload (STOL) JISC5201-1: 1998 Clause 4.132.5 times RCWV or max. overload voltage, for 5seconds		±1%: ΔR/R max. ±(1%+0.05Ω) No visible damage	<50mΩ	






Test	Durandum / Trad Mathed	Requirement		
	Procedure / Test Method	Resistor	0Ω	
Load life in Humidity JISC5201-1: 1998 Clause 4.24	1000 +48/-0 hours, loaded with RCWV or Vmax in humidity chamber controller at 40°C± 2°C and 90 to 95% relative humidity, 1.5hours on and 0.5 hours off	$\pm$ 1%: ΔR/R max. $\pm$ (1%+0.1Ω) No visible damage	<50mΩ	
Load life (endurance) JISC5201-1: 1998 Clause 4.25	1000 +48/-0 hours, loaded with RCWV or Vmax in chamber controller 70±2°C, 1.5 hours on and 0.5 hours off	$\pm$ 1%: ΔR/R max. $\pm$ (1%+0.1Ω) No visible damage	<50mΩ	
Insulation Resistance JISC5201-1: 1998 Clause 4.6	Apply the maximum overload voltage (DC) for 1minute	R≧10GΩ		
Dielectric Withstand Voltage JISC5201-1: 1998 Clause 4.7	Apply the maximum overload voltage (AC) for 1 minute	No breakdown or flashover		

# **Test Condition For Jumper (0** Ω)

Item	MCWR12	MCWR08	MCWR06	MCWR04		
Power Rating At 70°C	1/4W	1/8W	1/10W	1/16W		
Resistance	MAX. 50mΩ					
Rated Current	2A	1.5A	1A	1A		
Peak Current	5A	3.5A	3A	2A		
Operating Temperature		-55°C to	+155° C			

# Packaging:

### Paper Tape specifications




**Dimensions : Millimetres** 





Series No.	А	В	w	F	E
MCWR12	3.6 ±0.2	2 ±0.2		3.5 ±0.2	1.75 ±0.1
MCWR08	2.4 ±0.2	1.65 ±0.2	8 ±0.3		
MCWR06	1.9 ±0.2	1.1 ±0.2			
MCWR04	1.2 ±0.1	0.7 ±0.1			
Series No.	P1	P0	D	т	
MCWR12/WR08	4.10.4			Max. 1	
MCWR06	4 ±0.1	4 ±0.1	Φ1.5 <sup>+0.1</sup> -0.0	+0.1 -0.0 0.65 ±0.05	
MCWR04	2 ±0.1			0.4 ±0.05	1

# 7" Reel dimensions:



Symbol	A	В	С	D
7" reel	Φ178 ±2	Φ60 ±1	13 ±0.2	9 ±0.5
10" reel	Φ254 ±2	Φ100 ±1	13 ±0.2	9 ±0.5
13" reel	Ф330 ±2	Φ100 ±1	13 ±0.2	9 ±0.5

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

