

**BLACK DRYWIPE INK - WB7311.1**

**SAFETY DATA SHEET**

(REACH regulation (EC) n° 1907/2006 - n° 453/2010)

**SECTION 1 : IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING**

**1.1. Product identifier**

Product name : BLACK DRYWIPE INK

Product code : WB7311.1.

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

Ink for BEROL: Drywipe Pen, Drywipe Marker

**1.3. Details of the supplier of the safety data sheet**

Registered company name : Newell Rubbermaid UK Limited.

Address : Halifax Ave - Fradley Park .WS 13 8SS.Lichfield Staffordshire.United Kingdom.

Telephone : +44 (0) 1543447001. Fax : .

Aftersales.SERVICE@newellco.com

www.newellrubbermaid.com

**1.4. Emergency telephone number : 0845 4647.**

Association/Organisation : National Poisons Information Service.

**SECTION 2 : HAZARDS IDENTIFICATION**

**2.1. Classification of the substance or mixture**

**In compliance with EC regulation No. 1272/2008 and its amendments.**

Flammable liquid, Category 2 (Flam. Liq. 2, H225).

Specific target organ toxicity (single exposure), Category 3 (STOT SE 3, H336).

This mixture does not present an environmental hazard. No known or foreseeable environmental damage under standard conditions of use.

**In compliance with directives 67/548/EEC, 1999/45/EC and their amendments.**

Highly flammable (F, R 11).

Vapours may cause drowsiness and dizziness (R 67).

This mixture does not present an environmental hazard. No known or foreseeable environmental damage under standard conditions of use.

**2.2. Label elements**

**In compliance with EC regulation No. 1272/2008 and its amendments.**

Hazard pictograms :



GHS07



GHS02

Signal Word :

DANGER

Product identifiers :

603-064-00-3

MONOPROPYLENE GLYCOL METHYL ETHER

Hazard statements :

H225

Highly flammable liquid and vapour.

H336

May cause drowsiness or dizziness.

**BLACK DRYWIPE INK - WB7311.1**

Precautionary statements - General :

P101 If medical advice is needed, have product container or label at hand.  
P102 Keep out of reach of children.

Precautionary statements - Prevention :

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
P240 Ground/bond container and receiving equipment.  
P261 Avoid breathing dust/fume/gas/mist/vapours/spray.  
P271 Use only outdoors or in a well-ventilated area.

Precautionary statements - Response :

P312 Call a POISON CENTER/doctor/.../if you feel unwell.  
P370 + P378 In case of fire: Use... to extinguish.

Precautionary statements - Storage :

P403 + P233 Store in a well-ventilated place. Keep container tightly closed.  
P403 + P235 Store in a well-ventilated place. Keep cool.  
P405 Store locked up.

Precautionary statements - Disposal :

P501 Dispose of contents/container to ...

**2.3. Other hazards**

The mixture does not contain substances classified as 'Substances of Very High Concern' (SVHC)  $\geq 0.1\%$  published by the European Chemicals Agency (ECHA) under article 57 of REACH: <http://echa.europa.eu/fr/candidate-list-table>

The mixture satisfies neither the PBT nor the vPvB criteria for mixtures in accordance with annexe XIII of the REACH regulations EC 1907/2006.

**SECTION 3 : COMPOSITION/INFORMATION ON INGREDIENTS**

**3.2. Mixtures**

**Composition :**

Identification	(EC) 1272/2008	67/548/EEC	Note	%
INDEX: 603-002-00-5 CAS: 64-17-5 EC: 200-578-6  ETHANOL	GHS02 Dgr Flam. Liq. 2, H225	F F;R11	[1]	50 $\leq$ x % < 100
INDEX: 603-064-00-3 CAS: 107-98-2 EC: 203-539-1  MONOPROPYLENE GLYCOL METHYL ETHER	GHS02, GHS07 Wng Flam. Liq. 3, H226 STOT SE 3, H336	R10 R67	[1]	10 $\leq$ x % < 25

**Information on ingredients :**

[1] Substance for which maximum workplace exposure limits are available.

**SECTION 4 : FIRST AID MEASURES**

As a general rule, in case of doubt or if symptoms persist, always call a doctor.

NEVER induce swallowing by an unconscious person.

**4.1. Description of first aid measures**

**In the event of exposure by inhalation :**

In the event of massive inhalation, remove the person exposed to fresh air. Keep warm and at rest.

**BLACK DRYWIPE INK - WB7311.1**

---

If the person is unconscious, place in recovery position. Notify a doctor in all events, to ascertain whether observation and supportive hospital care will be necessary.

If breathing is irregular or has stopped, effect mouth-to-mouth resuscitation and call a doctor.

**In the event of swallowing :**

Seek medical attention, showing the label.

**4.2. Most important symptoms and effects, both acute and delayed**

No data available.

**4.3. Indication of any immediate medical attention and special treatment needed**

No data available.

---

**SECTION 5 : FIREFIGHTING MEASURES**

Flammable.

Chemical powders, carbon dioxide and other extinguishing gas are suitable for small fires.

**5.1. Extinguishing media**

Keep packages near the fire cool, to prevent pressurised containers from bursting.

**Suitable methods of extinction**

Prevent the effluent of fire-fighting measures from entering drains or waterways.

**5.2. Special hazards arising from the substance or mixture**

A fire will often produce a thick black smoke. Exposure to decomposition products may be hazardous to health.

Do not breathe in smoke.

In the event of a fire, the following may be formed :

- carbon monoxide (CO)
- carbon dioxide (CO<sub>2</sub>)

**5.3. Advice for firefighters**

Fire-fighting personnel are to be equipped with autonomous insulating breathing apparatus.

---

**SECTION 6 : ACCIDENTAL RELEASE MEASURES**

**6.1. Personal precautions, protective equipment and emergency procedures**

Consult the safety measures listed under headings 7 and 8.

**For non first aid worker**

Avoid inhaling the vapors.

If a large quantity has been spilt, evacuate all personnel and only allow intervention by trained operators equipped with safety apparatus.

**For first aid worker**

First aid workers will be equipped with suitable personal protective equipment (See section 8).

**6.2. Environmental precautions**

Contain and control the leaks or spills with non-combustible absorbent materials such as sand, earth, vermiculite, diatomaceous earth in drums for waste disposal.

Prevent any material from entering drains or waterways.

**6.3. Methods and material for containment and cleaning up**

Clean preferably with a detergent, do not use solvents.

**6.4. Reference to other sections**

No data available.

**BLACK DRYWIPE INK - WB7311.1**

---

**SECTION 7 : HANDLING AND STORAGE**

Requirements relating to storage premises apply to all facilities where the mixture is handled.

**7.1. Precautions for safe handling**

Always wash hands after handling.

Remove and wash contaminated clothing before re-using.

**Fire prevention :**

Handle in well-ventilated areas.

Prevent the formation of flammable or explosive concentrations in air and avoid vapor concentrations higher than the occupational exposure limits.

Prevent the accumulation of electrostatic charges with connections to earth.

The mixture can become electrostatically charged : always earth during decanting operations. Wear antistatic shoes and clothing and floors should be electrically conductive.

Use the mixture in premises free of naked flames or other sources of ignition and ensure that electrical equipment is suitably protected.

Keep packages tightly closed and away from sources of heat, sparks and naked flames.

Do not use tools which may produce sparks. Do not smoke.

Prevent access by unauthorised personnel.

**Recommended equipment and procedures :**

For personal protection, see section 8.

Observe precautions stated on label and also industrial safety regulations.

Avoid inhaling vapors.

Avoid inhaling vapors. Carry out any industrial operation which may give rise to this in a sealed apparatus.

Provide vapor extraction at the emission source and also general ventilation of the premises.

Also provide breathing apparatus for certain short tasks of an exceptional nature and for emergency interventions.

In all cases, recover emissions at source.

**Prohibited equipment and procedures :**

No smoking, eating or drinking in areas where the mixture is used.

**7.2. Conditions for safe storage, including any incompatibilities**

No data available.

**Storage**

Keep out of reach of children.

Keep the container tightly closed in a dry, well-ventilated place.

Keep away from all sources of ignition - do not smoke.

Keep well away from all sources of ignition, heat and direct sunlight.

Avoid accumulation of electrostatic charges.

**Packaging**

Always keep in packaging made of an identical material to the original.

**7.3. Specific end use(s)**

No data available.

---

**SECTION 8 : EXPOSURE CONTROLS/PERSONAL PROTECTION**

**8.1. Control parameters**

**Occupational exposure limits :**

- European Union (2009/161/EU, 2006/15/EC, 2000/39/EC, 98/24/EC)

CAS	VME-mg/m3	VME-ppm	VLE-mg/m3	VLE-ppm	Notes
107-98-2	375	100	568	150	Peau

**BLACK DRYWIPE INK - WB7311.1**

- ACGIH TLV (American Conference of Governmental Industrial Hygienists, Threshold Limit Values, 2010) :

CAS	TWA :	STEL :	Ceiling :	Definition :	Criteria :
64-17-5	1000 ppm	-	-	-	-
107-98-2	100 ppm	150 ppm	-	-	-

- Germany - AGW (BAuA - TRGS 900, 21/06/2010) :

CAS	VME :	VME :	Excess	Notes
64-17-5	500 ml/m3	960 mg/m3	2(II)	DFG, Y
107-98-2	100 ml/m3	370 mg/m3	2(I)	DFG, Y

- France (INRS - ED984 :2008) :

CAS	VME-ppm :	VME-mg/m3 :	VLE-ppm :	VLE-mg/m3 :	Notes :	TMP No :
64-17-5	1000	1900	5000	9500	-	84
107-98-2	50	188	100	375	*	84

- UK / WEL (Workplace exposure limits, EH40/2005, 2007) :

CAS	TWA :	STEL :	Ceiling :	Definition :	Criteria :
64-17-5	1000 ppm	-	-	-	-
107-98-2	100 ppm	150 ppm	-	-	-

**8.2. Exposure controls**

**Personal protection measures, such as personal protective equipment**

Use personal protective equipment that is clean and has been properly maintained.

Store personal protective equipment in a clean place, away from the work area.

Never eat, drink or smoke during use. Remove and wash contaminated clothing before re-using. Ensure that there is adequate ventilation, especially in confined areas.

**- Eye / face protection**

Avoid contact with eyes.

Use eye protectors designed to protect against liquid splashes

Before handling, wear safety goggles in accordance with standard EN166.

**- Hand protection**

Use suitable protective gloves that are resistant to chemical agents in accordance with standard EN374.

Gloves must be selected according to the application and duration of use at the workstation.

Protective gloves need to be selected according to their suitability for the workstation in question : other chemical products that may be handled, necessary physical protections (cutting, pricking, heat protection), level of dexterity required.

Recommended properties :

- Impervious gloves in accordance with standard EN374

**- Body protection**

Work clothing worn by personnel shall be laundered regularly.

After contact with the product, all parts of the body that have been soiled must be washed.

**- Respiratory protection**

Avoid breathing vapours.

If the ventilation is insufficient, wear appropriate breathing apparatus.

When workers are confronted with concentrations that are above occupational exposure limits, they must wear a suitable, approved, respiratory protection device.

Anti-gas and vapour filter(s) (Combined filters) in accordance with standard EN14387 :

- A1 (Brown)

**BLACK DRYWIPE INK - WB7311.1**

---

**SECTION 9 : PHYSICAL AND CHEMICAL PROPERTIES**

**9.1. Information on basic physical and chemical properties**

**General information :**

Physical state : Fluid liquid.

**Important health, safety and environmental information**

pH : Not relevant.  
Boiling point/boiling range : > 35°C  
Flash Point : 13.00 °C.  
Explosive properties, lower explosivity limit (%) : 1.7  
Explosive properties, upper explosivity limit (%) : 15.0  
Vapour pressure (50°C) : Not relevant.  
Density : Not stated.  
Water solubility : Insoluble.  
Melting point/melting range : Not relevant.  
Self-ignition temperature : Not relevant.  
Decomposition point/decomposition range : Not relevant.

**9.2. Other information**

No data available.

---

**SECTION 10 : STABILITY AND REACTIVITY**

**10.1. Reactivity**

No data available.

**10.2. Chemical stability**

This mixture is stable under the recommended handling and storage conditions in section 7.

**10.3. Possibility of hazardous reactions**

No data available.

**10.4. Conditions to avoid**

Any apparatus likely to produce a flame or to have a metallic surface at high temperature (burners, electric arcs, furnaces etc.) must not be allowed on the premises.

Avoid :

- accumulation of electrostatic charges.
- heating
- heat
- flames and hot surfaces

**10.5. Incompatible materials**

**10.6. Hazardous decomposition products**

The thermal decomposition may release/form :

- carbon monoxide (CO)
- carbon dioxide (CO<sub>2</sub>)

**BLACK DRYWIPE INK - WB7311.1**

---

**SECTION 11 : TOXICOLOGICAL INFORMATION**

**11.1. Information on toxicological effects**

Narcotic effects may occur, such as drowsiness, narcosis, decreased alertness, loss of reflexes, lack of coordination or dizziness.

Effects may also occur in the form of violent headaches or nausea, judgement disorder, giddiness, irritability, fatigue or memory disturbance.

**11.1.1. Substances**

No toxicological data available for the substances.

**11.1.2. Mixture**

No toxicological data available for the mixture.

**Monograph(s) from the IARC (International Agency for Research on Cancer) :**

CAS 64-17-5 : IARC Group 1 : The agent is carcinogenic to humans.

**SECTION 12 : ECOLOGICAL INFORMATION**

**12.1. Toxicity**

**12.1.2. Mixtures**

No aquatic toxicity data available for the mixture.

**12.2. Persistence and degradability**

No data available.

**12.3. Bioaccumulative potential**

No data available.

**12.4. Mobility in soil**

No data available.

**12.5. Results of PBT and vPvB assessment**

No data available.

**12.6. Other adverse effects**

No data available.

**German regulations concerning the classification of hazards for water (WGK) :**

WGK 1 (VwVwS vom 27/07/2005, KBws) : Slightly hazardous for water.

**SECTION 13 : DISPOSAL CONSIDERATIONS**

Proper waste management of the mixture and/or its container must be determined in accordance with Directive 2008/98/EC.

**13.1. Waste treatment methods**

Do not pour into drains or waterways.

**Waste :**

Waste management is carried out without endangering human health, without harming the environment and, in particular without risk to water, air, soil, plants or animals.

Recycle or dispose of waste in compliance with current legislation, preferably via a certified collector or company.

Do not contaminate the ground or water with waste, do not dispose of waste into the environment.

**Soiled packaging :**

Empty container completely. Keep label(s) on container.

Give to a certified disposal contractor.

**BLACK DRYWIPE INK - WB7311.1**

**SECTION 14 : TRANSPORT INFORMATION**

Transport product in compliance with provisions of the ADR for road, RID for rail, IMDG for sea and ICAO/IATA for air transport (ADR 2013 - IMDG 2012 - ICAO/IATA 2014).

**14.1. UN number**

3175

**14.2. UN proper shipping name**

UN3175=SOLIDS or mixtures of solids (such as preparations and wastes) CONTAINING FLAMMABLE LIQUID, N.O.S. having a flash-point up to 60 °C

**14.3. Transport hazard class(es)**

- Classification :



4.1

**14.4. Packing group**

II

**14.5. Environmental hazards**

-

**14.6. Special precautions for user**

ADR/RID	Class	Code	Pack gr.	Label	Ident.	LQ	Provis.	EQ	Cat.	Tunnel
	4.1	F1	II	4.1	40	1 kg	216 274 601	E2	2	E

IMDG	Class	2°Label	Pack gr.	LQ	EMS	Provis.	EQ
	4.1	-	II	1 kg	F-A,S-I	216 274	E2

IATA	Class	2°Label	Pack gr.	Passager	Passager	Cargo	Cargo	note	EQ
	4.1	-	II	445	15 kg	448	50 kg	A46	E2
	4.1	-	II	Y441	5 kg	-	-	A46	E2

For limited quantities, see part 2.7 of the OACI/IATA and chapter 3.4 of the ADR and IMDG.

For excepted quantities, see part 2.6 of the OACI/IATA and chapter 3.5 of the ADR and IMDG.

**14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code**

No data available.

**SECTION 15 : REGULATORY INFORMATION**

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

**- Classification and labelling information included in section 2:**

The following regulations have been used:

- Directive 67/548/EEC and its adaptations
- Directive 1999/45/EC and its adaptations
- EU Regulation No. 1272/2008 amended by EU Regulation No. 487/2013.
- EU Regulation No. 1272/2008 amended by EU Regulation No. 758/2013.
- EU Regulation No. 1272/2008 amended by EU Regulation No. 944/2013.
- EU Regulation No. 1272/2008 amended by EU Regulation No. 605/2014.



**BLACK DRYWIPE INK - WB7311.1**

**- Container information:**

The mixture is contained in packaging that does not exceed 125 ml.  
Containers to be fitted with a tactile warning of danger (see EC Regulation No. 1272/2008, Annex II, Part 3).

**- Particular provisions :**

No data available.

**- German regulations concerning the classification of hazards for water (WGK) :**

WGK 1 (VwVwS vom 27/07/2005, KBws) : Slightly hazardous for water.

**15.2. Chemical safety assessment**

No data available.

**SECTION 16 : OTHER INFORMATION**

Since the user's working conditions are not known by us, the information supplied on this safety data sheet is based on our current level of knowledge and on national and community regulations.

The mixture must not be used for other uses than those specified in section 1 without having first obtained written handling instructions.

It is at all times the responsibility of the user to take all necessary measures to comply with legal requirements and local regulations.

The information in this safety data sheet must be regarded as a description of the safety requirements relating to the mixture and not as a guarantee of the properties thereof.

**In compliance with directives 67/548/EEC, 1999/45/EC and their amendments.**

Hazard symbols :



Highly flammable

Risk phrase :

R 11 Highly flammable.  
R 67 Vapours may cause drowsiness and dizziness.

Safety phrase :

S 2 Keep out of the reach of children.  
S 46 If swallowed, seek medical advice immediately and show this container or label.  
S 16 Keep away from sources of ignition - No smoking.  
S 51 Use only in well-ventilated areas.  
S 9 Keep container in a well-ventilated place.

**Title for H, EUH and R indications mentioned in section 3 :**

H225 Highly flammable liquid and vapour.  
H226 Flammable liquid and vapour.  
H336 May cause drowsiness or dizziness.  
R 10 Flammable.  
R 11 Highly flammable.  
R 67 Vapours may cause drowsiness and dizziness.

**Abbreviations :**

ADR : European agreement concerning the international carriage of dangerous goods by Road.  
IMDG : International Maritime Dangerous Goods.  
IATA : International Air Transport Association.  
ICAO : International Civil Aviation Organisation  
RID : Regulations concerning the International carriage of Dangerous goods by rail.  
WGK : Wassergefährdungsklasse (Water Hazard Class).

**BLACK DRYWIPE INK - WB7311.1**

---

GHS02 : Flame

GHS07 : Exclamation mark