Radial Leaded PTC Resettable Fuse







Applications

Line Voltage Power Supply, Transformer and Appliances

Features

- Low hold current, solid state, Radial leaded product ideal for up to 265V AC/DC.
- · Operation Current from 0.05A to 2A
- Maximum Voltage 240V AC/DC
- Maximum Interrupt Voltage 265V AC/DC
- Temperature range: -40°C to +85°C for MC011373 to MC011380
 -20°C to +85°C for MC011381 to MC011385

Electrical Characteristics (23°C)

Part Number	Hold Current	Trip Current	Max. Time to trip	Max. Current	Rated Voltage	Max. Int. Voltage	Typ. Power	Resistance	
								RMIN	R ₁ MAX
	Ін, А	lτ, A	at 5×Iн, S	Imax, A	V _{MAX} , V AC/DC	VI-MAX, V AC/DC	Pd, W	Ω	Ω
MC011373	0.05	0.12	15	1	240	265	0.7	18.5	65
MC011374	0.08	0.19	15	1.2	240	265	0.8	7.4	26
MC011375	0.12	0.3	15	1.2	240	265	1	3	12
MC011376	0.16	0.37	15	2	240	265	1.4	2.5	7.8
MC011377	0.25	0.56	18.5	3.5	240	265	1.5	1.3	3.8
MC011378	0.33	0.74	21	4.5	240	265	1.7	0.83	2.6
MC011379	0.4	0.9	24	5.5	240	265	2	0.6	1.9
MC011380	0.55	1.25	26	7	240	265	3.4	0.45	1.45
MC011381	0.75	1.5	18	7.5	240	265	2.6	0.32	0.84
MC011382	1	2	21	10	240	265	2.9	0.22	0.58
MC011383	1.25	2.5	23	12.5	240	265	3.3	0.17	0.44
MC011384	1.5	3	23	15	240	265	3.7	0.12	0.32
MC011385	2	4	28	20	240	265	4.5	0.09	0.22

Ін = Hold current-maximum current at which the device will not trip at 23°C still air.

 I_T = Trip current-minimum current at which the device will always trip at 23°C still air.

VMAX = Maximum voltage device can withstand without damage at its rated current.

IMAX = Maximum fault current device can withstand without damage at rated voltage (V max).

Pd = Typical power dissipated from device when in the tripped state in 23°C still air environment.

RMIN = Minimum device resistance at 23°C.

R_{1MAX} = Maximum device resistance at 23°C 1 hour after tripping.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands



Radial Leaded PTC Resettable Fuse



Physical Specifications

Lead Material : MC011373, MC011374, MC011375 & MC011376 - Electrolytic tin plated copper, 24AWG.

MC011377, MC011378 & MC011379 - Electrolytic tin plated copper, 22AWG.

MC011380, MC011381, MC011382, MC011383, MC011384 & MC011385 - Electrolytic tin plated

copper, 20AWG.

Soldering Characteristics : MIL-STD-202, Method 208E.

Insulating Coating : Flame retardant epoxy, meets UL-94V-0 requirement.

Dimensions




Figure 1

Lead Size: 24AWG Φ0.51mm Diameter




Figure 2

Lead Size: 22AWG Φ0.65mm Diameter




Figure 3

Lead Size: 20AWG Φ0.81mm Diameter




Figure 4

Lead Size: 20AWG Φ0.81mm Diameter


Part Number		Α	В	С	D	Е	F
	Figure	Maximum	Maximum	Typical	Minimum	Maximum	Typical
MC011373	1	8.3	10.7	5.1	7.6	3.8	1.6
MC011374	1	8.3	10.7	5.1	7.6	3.8	1.6
MC011375	1	8.3	10.7	5.1	7.6	3.8	1.6
MC011376	1	9.9	12.5	5.1	7.6	3.8	1.6
MC011377	2	9.6	17.4	5.1	7.6	3.8	1.8
MC011378	2	11.4	16.5	5.1	7.6	3.8	1.8
MC011379	2	11.5	19.5	5.1	7.6	3.8	1.8
MC011380	3	14	21.7	5.1	7.6	4.1	1.9
MC011381	3	11.5	23.4	5.1	7.6	4.8	1.9
MC011382	4	18.7	24.4	10.2	7.6	5.1	1.9
MC011383	4	21.2	27.4	10.2	7.6	5.3	1.9
MC011384	4	23.4	30.9	10.2	7.6	5.3	1.9
MC011385	3	24.9	33.8	10.2	7.6	6.1	1.9

Dimensions: Millimetres

Radial Leaded PTC Resettable Fuse


multicomp PRO

Thermal Derating Curve



A: MC011373 MC011374 MC011375 MC011376 MC011377 MC011378 MC011380 B: MC011380 MC011381 MC011382 MC011383 MC011384 MC011385

Typical Time-To-Trip at 23°C



A = MC011373 **B** = MC011374 **C** = MC011375 **D** = MC011376 **E** = MC011377

F = MC011377G = MC011379 **H** = MC011380

I = MC011381 J = MC011382

K = MC011383 **L** = MC011384

M = MC011385

Part Number Table

Description	Part Number	
PTC Resettable Fuse, 0.05A, 240V AC/DC, Through Hole	MC011373	
PTC Resettable Fuse, 0.08A, 240V AC/DC, Through Hole	MC011374	
PTC Resettable Fuse, 0.12A, 240V AC/DC, Through Hole	MC011375	
PTC Resettable Fuse, 0.16A, 240V AC/DC, Through Hole	MC011376	
PTC Resettable Fuse, 0.25A, 240V AC/DC, Through Hole	MC011377	
PTC Resettable Fuse, 0.33A, 240V AC/DC, Through Hole	MC011378	
PTC Resettable Fuse, 0.4A, 240V AC/DC, Through Hole	MC011379	
PTC Resettable Fuse, 0.55A, 240V AC/DC, Through Hole	MC011380	
PTC Resettable Fuse, 0.75A, 240V AC/DC, Through Hole	MC011381	
PTC Resettable Fuse, 1A, 240V AC/DC, Through Hole	MC011382	
PTC Resettable Fuse, 1.25A, 240V AC/DC, Through Hole	MC011383	
PTC Resettable Fuse, 1.5A, 240V AC/DC, Through Hole	MC011384	
PTC Resettable Fuse, 2A, 240V AC/DC, Through Hole	MC011385	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

