


# PRODUCT DATA SHEET

Part Number: 1884XXXXX

Type	Size	Rating	Description
LED	E14	AC/DC	Edison Screw LED Lamp



Part #	Voltage (V)	Colour	AC Current (mA)	Intensity (mcd)
1884635W3D	24	White Diffuse	17	2500
1884665W3D	48	White Diffuse	8.5	2500
1884675W3D	60	White Diffuse	8.5	2500
18846A5W3D	85	White Diffuse	8.5	2500
1884713W3D	130	White Diffuse	5	2500
1884723W3D	230	White Diffuse	5	2500

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 BA15s Lamp base
- 3 Storage temperature -25 °C to +80°C
- 4 Application temperature -20 °C to +60°C
- 5 Due to component tolerances, colour temperature variations may be observed
- 6 The plastic(polycarbonate) has limited chemical resistance
- 7 RoHS & REACH SVHC compliant