

## Platform scales DE-D



### Application:

For versatile use in various locations such as production, warehousing and shipping.

### Execution:

- Dual range scales with automatic switch-over
- Display unit (degree of protection IP65) with 1.5 m cable
- Options: Stand for display unit
- Freely-programmable weighing unit, e.g. displays in thread length g/m, paper weight g/m<sup>2</sup>
- Formulation function for weighing different components
- Backlit LCD display with 25 mm digit size

### Advantage:

- Dual measurement display for finer digit increment and higher accuracy in the initial weighing range
- **Versatile positioning of display unit, free-standing or bolted to scales**

### Delivery:

Mains adapter



|                                      |                  |
|--------------------------------------|------------------|
| <b>Art. no.</b>                      | <b>44618 210</b> |
| <b>Brand</b>                         | KERN             |
| <b>Manufacturer Part Number</b>      | DE 15K0.2D       |
| <b>Type description</b>              | DE 15K0.2D       |
| <b>Max. weight measuring range</b>   | 6 kg             |
| <b>Max. weight measuring range 2</b> | 15 kg            |
| <b>Digit increment, weight</b>       | 0.2 g            |
| <b>Digit increment 2, weight</b>     | 0.5 g            |
| <b>Plate size</b>                    | 315 x 305 mm     |
| <b>With unit counting</b>            | Yes              |
| <b>Min. item weight</b>              | 0.4 g            |
| <b>Reproducibility</b>               | 0.2 g            |
| <b>Reproducibility 2</b>             | 0.5 g            |
| <b>Linearity</b>                     | 0.8 g            |
| <b>Linearity 2</b>                   | 2 g              |
| <b>Data transmission type</b>        | RS232            |
| <b>Gross Weight</b>                  | 7.800 kg         |
| <b>Product Group</b>                 | 447              |

### EAN

4045761111219