

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: JENOLITE LOW STRENGTH THREADLOCKER

Product code: 89031

Synonyms: 390000

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Anaerobic adhesive / sealant.

1.3. Details of the supplier of the safety data sheet

Company name: Jenolite UK Ltd
Chater Lea Buildings
Letchworth
Hertfordshire
SG6 1WT

Tel: 01462 480764 **Email:**
Sales@Jenolite.com

1.4. Emergency telephone number

Emergency tel: 01462 480764
(office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Aquatic Acute 1: H400; Aquatic Chronic 2: H411; Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317; STOT SE 3: H335; -: EUH208

Most important adverse effects: Contains 1-acetyl-2-phenylhydrazine, hydroquinone monomethyl ether. May produce an allergic reaction. Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation. May cause respiratory irritation. Very toxic to aquatic life. Toxic to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: EUH208: Contains 1-acetyl-2-phenylhydrazine, hydroquinone monomethyl ether. May produce an allergic reaction.
H315: Causes skin irritation.
H317: May cause an allergic skin reaction.
H319: Causes serious eye irritation.
H335: May cause respiratory irritation.

SAFETY DATA SHEET

JENOLITE LOW STRENGTH THREADLOCKER

Page: 2

H400: Very toxic to aquatic life.

H411: Toxic to aquatic life with long lasting effects.

Hazard pictograms: GHS07: Exclamation mark

GHS09: Environmental



Signal words: Warning

Precautionary statements: P261: Avoid breathing spray.

P264: Wash contaminated skin thoroughly after handling.

P271: Use only outdoors or in a well-ventilated area.

P273: Avoid release to the environment.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P302+P352: IF ON SKIN: Wash with plenty of water.

P304+P340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P312: Call a POISON CENTRE or doctor if you feel unwell.

P321: Specific treatment (see information on this label)

P332+P313: If skin irritation occurs: Get medical advice/attention.

P337+P313: If eye irritation persists: Get medical advice/attention.

P403+P233: Store in a well-ventilated place. Keep container tightly closed.

P501: Dispose of contents/container to comply with Local, National and International regulations.

Haz. ingredients (label): POLYGLYCOL DIMETHACRYLATE; BIS(ISOPROPYL)NAPHTHALENE; HYDROXYALKYL METHACRYLATE; CUMENE HYDROPEROXIDE; ACRYLIC ACID

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

TRIETHYLENE GLYCOL DIMETHACRYLATE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
203-652-6	109-16-0	-	Skin Sens. 1: H317	30-50%

[cont...]

SAFETY DATA SHEET

JENOLITE LOW STRENGTH THREADLOCKER

Page: 3

BIS(ISOPROPYL)NAPHTHALENE

254-052-6	38640-62-9	-	Aquatic Acute 1: H400; Aquatic Chronic 2: H411	30-50%
-----------	------------	---	--	--------

HYDROXYALKYL METHACRYLATE

248-666-3	27813-02-1	-	STOT SE 3: H335; Eye Irrit. 2: H319; Skin Sens. 1: H317	2.9-10%
-----------	------------	---	---	---------

CUMENE HYDROPEROXIDE

201-254-7	80-15-9	-	Org. Perox. EF: H242; Acute Tox. 3: H331; Acute Tox. 4: H312; Acute Tox. 4: H302; STOT RE 2: H373; Skin Corr. 1B: H314; Aquatic Chronic 2: H411	1-2.9%
-----------	---------	---	---	--------

ACRYLIC ACID

201-177-9	79-10-7	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Acute Tox. 4: H302; Skin Corr. 1A: H314; Aquatic Acute 1: H400	<1%
-----------	---------	---	--	-----

N,N-DIMETHYL-P-TOLUIDINE

202-805-4	99-97-8	-	Acute Tox. 3: H331; Acute Tox. 3: H311; Acute Tox. 3: H301; STOT RE 2: H373; Aquatic Chronic 3: H412	<1%
-----------	---------	---	--	-----

1-ACETYL-2-PHENYLHYDRAZINE

204-055-3	114-83-0	-	Acute Tox. 3: H301+H311; Skin Irrit. 2: H315; STOT SE 3: H335; Aquatic Chronic 1: H410; Eye Irrit. 2: H319; Skin Sens. 1B: H317	<1%
-----------	----------	---	---	-----

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin.

Drench the affected skin with running water for 10 minutes or longer if substance is still on skin. Consult a doctor.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Do not induce vomiting. If conscious, give half a litre of water to drink immediately. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur. There may be vomiting.

[cont...]

SAFETY DATA SHEET

JENOLITE LOW STRENGTH THREADLOCKER

Page: 4

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. The floor of the storage room must be impermeable to prevent the escape of liquids.

[cont...]

SAFETY DATA SHEET
JENOLITE LOW STRENGTH THREADLOCKER

Page: 5

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

ACRYLIC ACID

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	30 mg/m ³	60 mg/m ³	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. The floor of the storage room must be impermeable to prevent the escape of liquids.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Impermeable gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Impermeable protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Purple

Odour: Perceptible odour

Evaporation rate: Negligible

Oxidising: No data available.

Solubility in water: Insoluble

Viscosity: No data available.

Boiling point/range°C: >35

Melting point/range°C: Not applicable.

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: >93

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: No data available.

Vapour pressure: <=666.6 Pa

Relative density: 1.1

pH: Not applicable.

VOC g/l: <15

[cont...]

SAFETY DATA SHEET
JENOLITE LOW STRENGTH THREADLOCKER

Page: 6

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat. Light.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

CUMENE HYDROPEROXIDE

ORL	MUS	LDLO	5	gm/kg
ORL	RAT	LD50	382	mg/kg
SCU	RAT	LD50	382	mg/kg

ACRYLIC ACID

IPR	RAT	LD50	22	mg/kg
ORL	MUS	LD50	830	mg/kg
ORL	RAT	LD50	1250	mg/kg
SCU	MUS	LD50	1590	mg/kg

N,N-DIMETHYL-P-TOLUIDINE

IPR	MUS	LD50	212	mg/kg
-----	-----	------	-----	-------

[cont...]

SAFETY DATA SHEET

JENOLITE LOW STRENGTH THREADLOCKER

Page: 7

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	DRM	Hazardous: calculated
STOT-single exposure	INH	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur. There may be vomiting.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Not biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No data available.

12.4. Mobility in soil

Mobility: No data available.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Toxic to aquatic organisms. Toxic to soil organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

[cont...]

SAFETY DATA SHEET

JENOLITE LOW STRENGTH THREADLOCKER

Page: 8

Section 14: Transport information

14.1. UN number

UN number: UN3082

14.2. UN proper shipping name

Shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.
(BIS(ISOPROPYL)NAPHTHALENE; ACRYLIC ACID)

14.3. Transport hazard class(es)

Transport class: 9

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: Yes

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: E

Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: EUH208: Contains 1-acetyl-2-phenylhydrazine, hydroquinone monomethyl ether. May produce an allergic reaction.

H226: Flammable liquid and vapour.

H242: Heating may cause a fire.

H301: Toxic if swallowed.

H301+H311: Toxic if swallowed or in contact with skin

H302: Harmful if swallowed.

H311: Toxic in contact with skin.

H312: Harmful in contact with skin.

H314: Causes severe skin burns and eye damage.

[cont...]

SAFETY DATA SHEET

JENOLITE LOW STRENGTH THREADLOCKER

Page: 9

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H331: Toxic if inhaled.

H332: Harmful if inhaled.

H335: May cause respiratory irritation.

H373: May cause damage to organs through prolonged or repeated exposure.

H400: Very toxic to aquatic life.

H410: Very toxic to aquatic life with long lasting effects.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.