

CNC short drill chuck

In accordance with ISO 7388-1 (DIN 69871) with clamping force booster



Application:

For use on machining centres and CNC milling machines with tool change.

Execution:


- Short design.
- Precision version.
- Easy tool change using hexagon T-handle wrench.
- Required pull stud no. 23690.

Advantage:

- Accident-proof as opening of the chuck during operation or on a sudden spindle stop is not possible.

Delivery:

1x CNC short drill chuck in accordance with ISO 7388-1 (DIN 69871) with clamping force booster.



Art. no.	21318 512
Brand	EWE
Manufacturer Part Number	805 532
Tool holding device	SK 40
Min./max. clamping width	1-13 mm
Projecting length	87.5 mm
Outer diameter	43 mm
Concentricity tolerance	0.04 mm
Coolant supply	No
Balancing quality	G 6.3 at 12 rpm
Gross Weight	1.383 kg
Product Group	208