

RES.CURRENT OP.CIRCUIT BREAKER TYPE AC WS
125A 3+N-POL IFN 0,5A 400V 4MW



Figure similar

Model		
product brand name		SENTRON
Product designation		RCCB
Design of the product		Instantaneous
General technical data		
Number of poles		4
Size of installation devices / acc. to DIN 43880		1
Protection against electrical shock		Finger and back-of-hand safe
circuit-breaker / Design		5SM3
Mechanical service life (switching cycles) / typical		10 000
Overvoltage category		III
Protection class		
Protection class IP		IP20, if the distribution board is installed, with connected conductors
Switching capacity		
Switching capacity current		
• acc. to EN 60898 / Rated value	kA	1.25
Dissipation		
Active power loss		
• for rated value of the current / with AC / in hot operating state / per pole	W	8.9
Electricity		
Tripping residual current / Rated value	mA	500

Current / with AC / Rated value	A	125
Surge current resistance / Rated value	kA	1

Product details

Product property		
<ul style="list-style-type: none"> • halogen-free 		Yes
<ul style="list-style-type: none"> • silicon-free 		Yes
Product expansion / can be installed / supplementary devices		Yes

Number

Number of test cycles / for environmental testing / acc. to IEC 60068-2-30		28
---	--	----

Connections

Connectable conductor cross-section / stranded		
<ul style="list-style-type: none"> • minimum 	mm ²	2.5
<ul style="list-style-type: none"> • maximum 	mm ²	50
Connectable conductor cross-section / solid		
<ul style="list-style-type: none"> • minimum 	mm ²	2.5
<ul style="list-style-type: none"> • maximum 	mm ²	50
Tightening torque / with screw-type terminals		
<ul style="list-style-type: none"> • minimum 	N·m	3
<ul style="list-style-type: none"> • maximum 	N·m	3.5
Position / of power supply cord		top or bottom

Mechanical Design




Height	mm	90
Width	mm	72
Depth	mm	77
mounting position		any
Installation depth	mm	70
Number of width units		4
Mounting type		DIN rail (REG)

Environmental conditions

Ambient temperature		
<ul style="list-style-type: none"> • minimum 	°C	-5
<ul style="list-style-type: none"> • maximum 	°C	45
<ul style="list-style-type: none"> • during storage / minimum permissible 	°C	-40
<ul style="list-style-type: none"> • during storage / maximum permissible 	°C	75

Certificates

Equipment marking		
<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 		F
<ul style="list-style-type: none"> • acc. to DIN EN 81346-2 		F

General Product Approval	Declaration of Conformity	Test Certificates	other
 GOST		other	 EG-Konf.
		other	Environmental Confirmations

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5SM37450>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/5SM37450/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SM37450

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015