

Universal chuck

For clamping micro drill bits and milling tools

ATORN®

Application

Extremely flexible extension for HYDRO expansion, shrink-fit and collets. For high precision centric clamping of milling, drilling and reaming tools.



Version

- Speed range up to 60,000 rpm
- Concentricity tolerance < 0.005 mm
- Very wide clamping range
- Chuck with spur gear

| | |
|---------------------------------|------------------|
| Art. No. | 23720 314 |
| Min./max. clamping width | 0.20-6.4 mm |
| Shaft diameter | 20 mm |
| Outer diameter | 25 mm |
| Length | 150 mm |
| Length 2 | 110 mm |
| Max. length | 154 mm |
| Max. tightening torque | 4 Nm |
| Torque transmission | 12 Nm |
| Concentricity tolerance | 0.005 mm |
| Coolant supply | Internal axial |
| Balancing quality | G 2.5 at 25 rpm |

EAN-Code

4050293358469