

COOLING UNIT DOOR OR WALL MOUNTED COOLING CAPACITY 640W 230 V AC RAL 7035 316X606X212 MM (WXHXD) INTERBAL CYCLE IP 54 OUTSIDE CYCLE IP 34

Model		
product brand name		SIVACON
Product designation		Cooling device
Design of the control cabinet cooler		Air/air

General technical data		
A-rated sound power level / maximum	dB	65
Operating pressure / maximum permissible	bar	25
Cooling capacity / at L35L35	W	640
Temperature		
• of the inner cooling circuit / minimum	°C	20
• of the inner cooling circuit / maximum	°C	46
• of the outer cooling circuit / minimum	°C	20

Electricity		
Starting current	A	8.1

Main circuit		
Operating voltage		
• with AC / at 50 Hz / Rated value / maximum	V	230
• with AC / at 60 Hz / Rated value / maximum	V	230
Operating current		
• of the fuse link / Rated value	A	6
• for motor / maximum rated value	A	2.1

Product details		
Product component		
• Heating		No
• Thermostat		Yes

Connections		
Type of electrical connection		Connector, 4-pole

Mechanical Design		
Height	mm	606
Width	mm	316
Depth	mm	212
Installation location		Mounting, full installation

Material	steel
----------	-------

Certificates

Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

E
E

General Product Approval



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR64235EG06>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR64235EG06/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR64235EG06

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015