

QM-Height height measuring device

With manual measuring slide, with air cushion device

Mitutoyo

Application:

For measuring external, internal, height, depth and distance dimensions and inner and outer diameters.

Execution:

- Manual measuring slide movement using handwheel
- Clear control panel with high contrast display
- ABSOLUTE electronic linear scale
- With air cushion system

Advantage:

- High-precision ABSOLUTE linear scale for position recording
- Automatic running of previously „learnt“ parts programmes
- GO/±NG assessment after setting the upper and lower tolerances.
- Frequently used functions are immediately accessed at the touch of a button
- Long service life

Delivery:

Includes dia. 5mm ball probe, calibration block, 4 x batteries LR6 (AA) 1.5 V



Art. no.	35173 040
Brand	MITUTOYO
Manufacturer Part Number	518-246
Length measuring range	600 mm
Min./max. application area with standard gauge slide carrier	0-715 mm
Digit increment (can be pre-selected)	0.001 mm, 0.005 mm
Perpendicularity tolerance (front)	12 µm
With air cushion equipment	Yes
Number of rechargeable batteries/batteries	4 PCS
Battery designation	Mignon AA
Type of rechargeable battery/battery	AlMn
Max. battery operating time	90 h
Gross Weight	32.000 kg
Product Group	3MB

EAN

4946368760629