

CBN sanding tips, cylindrical

Galvanic bond, grain B126



Application:

For grinding holes, radii and contours in stationary and manual applications

Execution:

- Single-layer coating with CBN grain

Advantage:

- Much less sensitive to heat than diamond grinding points



Art. no.	76056 110
Brand	PFERD
Manufacturer Part Number	4007220119389
Form	Cylindrical
Shank diameter	6 mm
Head diameter	6 mm
Length of head	6 mm
Shaft length	54 mm
Offset shank length	19 mm
Material of abrasive medium	CBN
Material to be processed	Case hardening steel, Tool steel, Hardened steel, Ball bearing steel
Grid size	B 126
Binding	Galvanic
Number of pieces per packet	1 PCS
Gross Weight	0.017 kg
Product Group	6AB

EAN

4007220119389