

# Han Megabit insert female 1 Entry, (GND)



Part number	09 14 008 3122
Specification	Han Megabit insert female 1 Entry, (GND)
HARTING eCatalogue	https://b2b.harting.com/09140083122

Image is for illustration purposes only. Please refer to product description.

#### Identification

Category	Inserts
Type of module	Han <sup>®</sup> Megabit module
Description of the module	Insert 2x 4 contacts
·	One entry

#### Version

Termination method	Crimp termination
Gender	Female
Number of contacts	8
further contacts	+ shielding
Details	With additional shield connection to the hinged frame Please order crimp contacts separately. Please order adapter module separately.

## Technical characteristics

Conductor cross-section	0.14 2.5 mm²
Rated current	10 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3



#### Technical characteristics

Rated current acc. to UL	2 A AWG 26 AWG 20 6 A AWG 18 8 A AWG 16 AWG 14
Rated voltage acc. to UL	30 V
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	100 Mbit/s
Contact resistance, shielding	≤100 mΩ
Limiting temperature	-40 +85 °C
Mating cycles	≥500

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

#### Commercial data

Packaging size	1
Net weight	43 g

Product data sheet 09 14 008 3122 Han Megabit insert female 1 Entry, (GND)



#### Commercial data

Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140020788
ETIM	EC000438
eCl@ss	27440218 Module for industrial connectors (data)