

Style C 6.3 (1/4").

**7010 Z** Standard bit, slotted, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
 Drive: DIN 3126, ISO 1173, style C 6.3.
 Application: For all types of screw applications in trade and industry.

Order-No.	⌀	↔	⊖	↳
01623	4.5	25	0.6	10
01624	5.5	25	0.8	10
01626	6.5	25	1.2	10
01627	8.0	25	1.6	10

Style C 6.3 (1/4").

**7011 Z** Standard bit, Phillips, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
 Drive: DIN 3126, ISO 1173, style C 6.3.
 Application: For all types of screw applications in trade and industry.

Order-No.	⊕	↔	↳
05298	PH0	25	10
01657	PH1	25	10
01658	PH2	25	10
01659	PH3	25	10
01649	PH4	32	10

**7010 Z L** Standard bit, slotted, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
 Drive: DIN 3126, ISO 1173, style C 6.3.
 Application: For all types of screw applications in trade and industry.

Order-No.	⌀	↔	⊖	↳
01604	3.0	39	0.5	10
01607	3.5	39	0.6	10
01606	4.0	39	0.5	10
01610	4.0	39	0.8	10
01609	4.5	39	0.6	10
01612	5.5	39	0.8	10
01613	5.5	39	1.0	10
01617	6.5	39	1.2	10
01619	8.0	39	1.2	10
01621	8.0	39	1.6	10

**NEW****7011 DWS** Drywall stop bit, Phillips, style C 6.3, in a plastic box.

Material: High grade chrome-vanadium steel, through hardened.
 Drive: DIN 3126, ISO 1173, style C 6.3.
 Application: The ideal bit for drywall constructors.
 Extra: The blue ring prevents the screw from being recessed too deeply into the plasterboard.

Order-No.	⊕	↔	↳
20150	PH2	25	10

**7012 Z** Standard bit, Pozidriv, style C 6.3.

Material: High grade chrome-vanadium steel, through hardened.
 Drive: DIN 3126, ISO 1173, style C 6.3.
 Application: For all types of screw applications in trade and industry.

Order-No.	⊕	↔	↳
05300	PZ0	25	10
01688	PZ1	25	10
01689	PZ2	25	10
01690	PZ3	25	10
01681	PZ4	32	10