

## Modular drilling system TDMX drilling depth 3xD

For universal use up to 1300 N/mm<sup>2</sup>, in diameter range of 16.00-40.00 mm

**WIDIA** 

### Execution:

- Drilling depth 3xD
- Diameter range 16-38 mm

### Advantage:

- Front clamping, possible to change the cutting body while clamped
- Up to 3x regrinding possible
- Polished chip grooves for better chip removal
- Types developed for material-specific applications



<b>Art. no.</b>	<b>11227 300</b>
<b>Brand</b>	WIDIA
<b>Manufacturer Part Number</b>	6572107
<b>Suitable for min. cutting diameter</b>	30 mm
<b>Suitable for max. cutting diameter</b>	30.99 mm
<b>Shank diameter</b>	32 mm
<b>Length</b>	204 mm
<b>Cantilever length</b>	144 mm
<b>Effective length</b>	93 mm
<b>Shaft length</b>	60 mm
<b>Suitable for indexable inserts type</b>	0
<b>Max. drilling depth (D)</b>	3xD
<b>Coolant supply</b>	Internal
<b>Tool holding device</b>	Parallel shank with chuck surface ISO 9766
<b>Bore type</b>	Normal bore, Stud hole bore, Cross bore, Slanted exit, Slanted entry
<b>Gross Weight</b>	0.839 kg
<b>Product Group</b>	1XB