

DVJN insert holder, negative right

For contour and longitudinal turning with VN indexable insert



Application:

For contour and longitudinal turning with VN indexable insert, 35°

Execution:

- Precision-manufactured steel support, burnished, hardened, adjustable clamping system, type V, pitch angle 93°, tip angle 35°, clearance angle 0°

Advantage:

- Streamlined geometry, optimised for contour lathe work with high feed depths and unfavourable conditions
- Negative body geometry ensures good stability and absorption of force for large cutting depths
- Wide adjustment range: Suitable for both finishing and rough machining
- Adjustable clamp minimises vibrations and ensures favourable power transmission

Art. no.	17684 106
Brand	WIDIA
Manufacturer Part Number	5696738
ISO name	DVJN R/L 2525 M16
Knife edge length	16 mm
Shaft height	25 mm
Shank width	25 mm
Length	150 mm
Programming size	32 mm
Suitable for indexable inserts	VN.. 1604..
Tool design	Right
Length of head	55 mm
Gross Weight	0.001 kg
Product Group	1XG

EAN

4050841487368