

## Workplace mat made of 100% nitrile rubber, oil-resistant

Flat structure, height 19 mm – modular assembly system



### Application:

Extremely comfortable anti-fatigue mat for heavy-duty work, with diamond-pattern surface. For use both in large areas and individual workplaces. These 45 x 45 cm modular floor tiles are equipped with a universal double locking system on all four sides, designed to enable an extra-firm, seamless connection for fast installation.

### Execution:

- This 19-mm thick mat lifts the employee off the hard floor, while balls underneath the mat allow for flexibility with every movement.
- The diamond-pattern surface provides good grip, and allows easy pivoting and freedom of movement when working on dynamic jobs
- Slip resistance R10 in accordance with DIN 51130
- Free of DOP, DMF, ozone-depleting substances, silicone and heavy metals

### Advantage:

- The square mats can be assembled to cover any area
- Can be combined with black or yellow edge strip made of nitrile rubber, 91 cm x 15 cm
- The flexible assembly system means that individual mats can be exchanged or adapted to a different environment
- Insulating mat protects against cold, heat, vibration and noise



<b>Art. no.</b>	<b>50225 262</b>
<b>Brand</b>	NOTRAX
<b>Manufacturer Part Number</b>	572S1818BL
<b>Surface structure</b>	Stud plate / closed
<b>Material</b>	Nitrile rubber
<b>Length</b>	450 mm
<b>Width</b>	450 mm
<b>Material thickness</b>	19 mm
<b>Mat design</b>	Individual mat
<b>Resistance against</b>	Oil, Acid (limited), Fats, Petrol, Coolant
<b>Suitable for wet areas</b>	No
<b>Antistatic</b>	No
<b>Anti-fatigue</b>	Yes
<b>Non-slip</b>	Yes
<b>Compliant with REACH</b>	Yes
<b>Colour</b>	Black
<b>ESD-capable</b>	No
<b>Gross Weight</b>	3.300 kg
<b>Product Group</b>	5AD

### EAN

066264190689 1