



SPECIFICATION

Mating Cycles	500
Filter type	C
Capacitance	3900pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	6dB
10	11dB
50	25dB
100	35dB
500	35dB
1000	32dB

PCB Layout, Component side, PCB thickness 1,6 mm

D  
C  
B  
A

Mg?Mstab/  
Scale  
1.5:1  
Blat/V Page  
2/3

Detail.	Dat.	Name
Insp.		
Stand.		

D-Sub, male, straight,  
25 Poles, turned solder pins,  
tin plated shell with dimples,  
spacer nuts and board-locks

09643227246	M3	33423	06/02/06	JMDR
09643227245	UNC 4-40	31058	8-JUL-02	CV
Part number	Nut thread	Mod.	Dat.	Name

HARTING EURL  
F-95972 Paris



TB 0964322724x

Sub.

All Dim. in mm  
Orig. Size DIN A 4