PTC-Resistor-Relay Type MSR820V 8 PTC-Circuits

MSR820V

Technical Data




The MSR820V monitors up to 8 PTC-resistor-circuits at the same time. A common relay signals an alarm or an error in a sensorcircuit.

The inputs can be enabled or disabled during operation. The MSR820V can also be used as a fault annuciator for collective reports

- 1-8 PTC-circuits, each 1...6 PTC in series (max. coldresistance 1500Ω/circuit)
- Easy activating/deactivating of PTC-circuits (display with LEDs)
- 2 potential-free relay-outputs, display of switching state with LEDs
- Display of state of PTC-circuits with 2 LEDs per circuit
- Electronic reclosing-lock (disconnectible with bridge Y1-Y2)
- monitoring of contacts for collective fault-reports

- Programmable functions:
 - Monitoring of short-circuit of PTCs (off / on)
 External Reset as normally closed (nc) or open (no) contact (Y1, Y2)
 - Power-fail-safe reclosing lock (off / on)
 - Function of relay
 - K1 and K2 closed-current mode
 - K1 and K2 operating-current mode
 - K1 closed- and K2 operating-current-mode
- Universal supply-voltage AC/DC 24 240 V
- Mounting on DIN-rail 35mm EN 60715 or wallmount (Option)
- Mounting height 55 mm

Order-number: T221709



BR 1: Wiedereinschaltsperre abgeschaltet

	Rated supply-voltage Us	AC/DC 24-240 V 0/50/60 Hz + 25/-20 %, <1W,<3VA DC 20,4 - 297 V AC 20 - 264 V
	Connectable PTC-resistors Switching Point	8 x 16 pieces according to DIN 44081/82 3,3 k Ω 4 k Ω typical 3,65 k Ω
	Output Relay Type of contact	2 x 1 change-over contact (CO) $AgSnO_2$
	Testing Conditions Rated ambient Temperature range	see "general technical informations" -20+55 °C
	Dimensions H x W x D Attachment	Design V4: 90 x 70 x 58 mm, mounting height 55 mm on rail NS 35 mm according to EN 60 715 or with screws M4 (option)
	Protection Housing / Terminals Weight	IP 30 / IP 20 app. 180 g