

[IMAGE]

Product Information

Product Category	MICROWAVES
Unit Barcode	5016368093740
Outer Carton Barcode	
Commodity Code	8516500000
Country of Origin	CHINA
Primary Colour	STAINLESS STEEL
Finish	PAINTED STEEL
Primary Material	PLASTIC
Warranty	2
Self Assembly	NO
Perishable Item	NO
Hazardous Item	NO

General Product Specification

Voltage	230
Frequency	50
Wattage	900
Rated Current	
Fuse Rating	
Plug Type	BS 1363
Cable Diameter	1
Cable Length	1.01
Class	CLASS I
Conformity Markings	CE+UKCA

Packaging & Shipping Information

Product Dimensions H x W x D (mm)	300	539	449
Packaged Dimensions H x W x D (mm)	366	608	480
Outer Carton Dimensions H x W x D (mm)			
Outer Carton Qty.			
Unit Weight (Kg)			19
Unit Packaged Weight (Kg)			20.4
Carton Weight (Kg)			
EPS (Kg)	0.36	PPT Exempt Plastic (Kg)	
Other Plastic (Kg)	0.054	Card / Paper (Kg)	1.53
Aluminium (Kg)		Steel (Kg)	

Category Specific Technical Information

Cavity Capacity	30	Freestanding or Built-in	FREESTANDING
Cavity Depth	362	Grill Function	YES
Cavity Height	223	Grill Output Power	
Cavity Material	STAINLESS STEEL	Housing Colour	SILVER
Cavity Width	354	Interior Light	YES
Control Panel Lock	YES	Inverter Technology	NO
Control Type	DIALS & BUTTONS	MAFF Rating	E
Convection Cooking Function	YES	Max Timer Value	
Convection Output Power		Microwave Output Power	900
Defrost Function	YES	Number of Auto Cooking Programmes	10
Digital Display	YES	Number of Microwave Power Levels	6
Door Hinge Position	LEFT	Turntable Diameter	315
Flatbed	NO	Turntable On/Off Function	