

# Single-phase, non-stabilized DC power supply GLC 400/24-5



Picture shows GLC 230/24-3


## Advantages

Fuse protection in the input and a fuse protection for the output
Separate windings
Capacitor switching at the output
Double screw terminals on the output
DC OK signalling via LEDs
Panel installation on mounting rails

## Applications

Robust DC power supply is concentrated on the core task of voltage and power supply.

## Sample application



## Standards

Non-stabilised dc power supply / Safety isolating transformer to VDE 0570 part 2-6, EN 61558-2-6, IEC 61558-2-6, UL 1012

## Approvals




UL 5085-1/-2, CSA 22.2 No.66



# Single-phase, non-stabilized DC power supply GLC 400/24-5

Type		GLC 400/24-5
Electrical data	Input	
	Input rated voltage	400 Vac
	Rated frequency	50 - 60 Hz
	Output	
	Output rated voltage	24 Vdc
	Power	120.00 W
	Output rated current	5.00 A
	Ripple factor	≤5 %
	Approvals	
	Approvals	cURus (transformer only)
	Environment	
	Type of cooling	self-cooling
	Ambient temperature max.	60 °C
	Safety and protection	
	Insulation class	E
	Protection index	IP 00
Safety class (prepared)	II	
Type	Enclosed	
Short circuit strength	short-circuit proof	
Order numbers		
Order Number	GLC 400/24-5	

Type		GLC 400/24-5
Mechanical data	Terminal and mounting	
	Fixing method	DIN Rail system TS35, additional with screws
	Terminals	Screw-type terminals
	Measures and weights	
	Weight	3.50 kg



Subject to change.