

## 3-jaw tapered rod lathe chuck DURO-T

Hand chuck in acc. with DIN 6350-1



### Application:

Optimised for turning applications, which require extremely high clamping forces, maximum concentricity and reliable continuous repeatability.

### Execution:

- Grease nipples with very easy access are located at each jaw position.
- Fast and regular lubrication to ensure a long service life
- For cylindrical self-centring adapter DIN 6350-1
- Large through-bore
- Chuck body surface hardened

### Advantage:

- No longer necessary to dismantle the chuck before lubricating the guides.
- With visual jaw locking and jaw quick-change system

### Delivery:

1 spanner, 1 set of fastening screws (DIN 6350-1) no. 22427 041-061 with undivided stepped jaws and no. 22428 041-051 with plain jaws and reverse top jaws



<b>Art. no.</b>	<b>22427 041</b>
<b>Brand</b>	RÖHM
<b>Manufacturer Part Number</b>	437476
<b>Outer diameter</b>	160 mm
<b>Number of jaws</b>	3
<b>DIN</b>	6350-1
<b>Min./max. external clamping width</b>	5-161 mm
<b>Min./max. internal clamping width</b>	67-174 mm
<b>Clearance hole</b>	42 mm
<b>Max. rotation speed</b>	5400
<b>Pitch circle diameter</b>	125 mm
<b>Centring diameter</b>	145 mm
<b>Tension force</b>	73 kN
<b>Max. torque</b>	120 Nm
<b>Gross Weight</b>	9.000 kg
<b>Product Group</b>	202

### EAN

4019208227740