


CUSTOMER	CPC
PRODUCT NO.	




CUSTOMER P/N:	CS21944	CS21945	CS21946	CS21946
L±T (mm)	1000 ± 10	2000 ± 20	3000 ± 30	5000 ± 40

NOTE:

- (1). Cable Spec: UL20276 (24+1) 30#: [(7/0, 10BC*1P+7/0, 10BC +FAM)*7PCS+7/0, 10BC*3C+7/0, 10BC*1P+AL+7/0, 12BC+B(112/0, 12ALM)]
- Jacket Material: PVC OD: 7.3 ± 0.2mm
- Cable Colour: Black
- Cable Printing: AWM 20276 80°C 30V VW-1
- DVI Digital/Analog Dual Link Cable
- (2). Connector A&B: DVI (24+1) PIN Male Solder Type
- Insulation: Black
- Contact: Gold Plated
- Shell: Gold Plated
- (3). Over Mold: PVC, Black
- (4). Parameter Settings: CT-8681FA
- (5). Packing: POLYBAG Packing

SIDE:A	SIDE:B	SIDE:A	SIDE:B
DVT24+1M	DVT24+1M	DVT24+1M	DVT24+1M
1 WHITE	1 WHITE	17 WHITE	17 WHITE
2 GREEN	2 GREEN	18 ORANGE	18 ORANGE
3 DRAIN	3 DRAIN	19 DRAIN	19 DRAIN
4 WHITE	4 WHITE	20 WHITE	20 WHITE
5 BLUE	5 BLUE	21 BLACK	21 BLACK
6 DRAIN	6 DRAIN	19 DRAIN	19 DRAIN
7 WHITE	7 WHITE	24 WHITE	24 WHITE
8 RED	8 RED	23 YELLOW	23 YELLOW
9 WHITE	9 WHITE	22 DRAIN	22 DRAIN
10 RED	10 RED	22 BRAID	22 BRAID
11 DRAIN	11 DRAIN	SHELL	SHELL
12 WHITE	12 WHITE	PAIR	PAIR
13 BROWN	13 BROWN	DRAIN WIRE OF PAIR	DRAIN WIRE OF PAIR
14 DRAIN	14 DRAIN		
15 YELLOW	15 YELLOW		
16 ORANGE	16 ORANGE		
16 VIOLET	16 VIOLET		

PIN OUT : (4)



GENERAL TOLERANCES (UNLESS SPECIFIED)

LENGTH: X, ± 1
 .X ± 0.2
 .XX ± 0.10
 ANGLE: X°, ± 1°
 .X° ± 0° 30'

UNIT: mm	REV: 00	HT-2351	NAME	DVT124+1PW/DVT124+1PM
DRAWING	XIAOCAO	2011/05/12	S. P. NO.	
CHECK			P. O. NO.	
APPROVE			SIZE	
			PAGE	1/1

00	NEW	2011/05/12
REV	DESCRIPTION	DATE