

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product form : Mixture  
Product name : JENOLITE STOP LEAK SEALER BLACK (IN TINS)-89242 NPD10543  
Product code : NPD10543

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

##### 1.2.1. Relevant identified uses

Intended for general public

##### 1.2.2. Uses advised against

No additional information available

#### 1.3. Details of the supplier of the safety data sheet

LMA SERVICES LTD  
Halifax Way Pocklington Industrial Estate  
YO42 1NR Pocklington – East Yorkshire  
England  
T 01759304676  
[technical@aerosol.uk.com](mailto:technical@aerosol.uk.com)

#### 1.4. Emergency telephone number

Emergency number : 01759304676

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH	0344 892 0111	Only for healthcare professionals

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Flammable liquids, Category 3 H226  
Specific target organ toxicity – Single exposure, Category 3, Narcosis H336  
Full text of H- and EUH-statements: see section 16

##### Adverse physicochemical, human health and environmental effects

Flammable liquid and vapour. May cause drowsiness or dizziness.

#### 2.2. Label elements

##### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS02

GHS07

Signal word (CLP) :

Warning

Contains :

Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics

Hazard statements (CLP) :

H226 - Flammable liquid and vapour.

H336 - May cause drowsiness or dizziness.

# JENOLITE STOP LEAK SEALER BLACK (IN TINS)-89242 NPD10543

## Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Precautionary statements (CLP) : P102 - Keep out of reach of children.  
P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
P271 - Use only outdoors or in a well-ventilated area.  
P501 - Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.

### 2.3. Other hazards

Contains no PBT/vPvB substances  $\geq 0.1\%$  assessed in accordance with REACH Annex XIII

The mixture does not contain substance(s) included in the list established in accordance with Article 59(1) of REACH for having endocrine disrupting properties, or is not identified as having endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at a concentration equal to or greater than 0,1 %

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable

### 3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics	EC-No.: 919-857-5	30 – 50	Flam. Liq. 3, H226 STOT SE 3, H336 Asp. Tox. 1, H304

Full text of H- and EUH-statements: see section 16

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

First-aid measures general : Call a poison center or a doctor if you feel unwell.  
First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing.  
First-aid measures after skin contact : Rinse skin with water/shower. Take off immediately all contaminated clothing.  
First-aid measures after eye contact : Rinse eyes with water as a precaution.  
First-aid measures after ingestion : Call a poison center or a doctor if you feel unwell.

### 4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects : May cause drowsiness or dizziness.

### 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.

### 5.2. Special hazards arising from the substance or mixture

Fire hazard : Flammable liquid and vapour.  
Hazardous decomposition products in case of fire : Toxic fumes may be released.

# JENOLITE STOP LEAK SEALER BLACK (IN TINS)-89242 NPD10543

## Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

### 5.3. Advice for firefighters

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

#### 6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area. No open flames, no sparks, and no smoking. Avoid breathing dust/fume/gas/mist/vapours/spray.

#### 6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

### 6.2. Environmental precautions

Avoid release to the environment.

### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Take up liquid spill into absorbent material. Notify authorities if product enters sewers or public waters.

Other information : Dispose of materials or solid residues at an authorized site.

### 6.4. Reference to other sections

For further information refer to section 13.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Precautions for safe handling : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Ground/bond container and receiving equipment. Use only non-sparking tools. Take precautionary measures against static discharge. Flammable vapours may accumulate in the container. Use explosion-proof equipment. Wear personal protective equipment. Use only outdoors or in a well-ventilated area. Avoid breathing dust/fume/gas/mist/vapours/spray.

Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

### 7.2. Conditions for safe storage, including any incompatibilities

Technical measures : Ground/bond container and receiving equipment.

Storage conditions : Store in a well-ventilated place. Keep cool. Keep container tightly closed. Store locked up.

### 7.3. Specific end use(s)

No additional information available

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### 8.1.1 National occupational exposure and biological limit values

No additional information available

#### 8.1.2. Recommended monitoring procedures

No additional information available

# JENOLITE STOP LEAK SEALER BLACK (IN TINS)-89242 NPD10543

## Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

### 8.1.3. Air contaminants formed

No additional information available

### 8.1.4. DNEL and PNEC

No additional information available

### 8.1.5. Control banding

No additional information available

## 8.2. Exposure controls

### 8.2.1. Appropriate engineering controls

#### Appropriate engineering controls:

Ensure good ventilation of the work station.

### 8.2.2. Personal protection equipment

#### Personal protective equipment symbol(s):



#### 8.2.2.1. Eye and face protection

##### Eye protection:

Safety glasses

#### 8.2.2.2. Skin protection

##### Skin and body protection:

Wear suitable protective clothing

##### Hand protection:

Protective gloves

#### 8.2.2.3. Respiratory protection

##### Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

#### 8.2.2.4. Thermal hazards

No additional information available

### 8.2.3. Environmental exposure controls

#### Environmental exposure controls:

Avoid release to the environment.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Black.
Odour	: characteristic.
Odour threshold	: Not available
Melting point	: Not applicable
Freezing point	: Not available
Boiling point	: Not available
Flammability	: Flammable liquid and vapour.
Explosive limits	: Not available
Lower explosion limit	: Not available
Upper explosion limit	: Not available
Flash point	: $\geq 40$ °C
Auto-ignition temperature	: Not available

# JENOLITE STOP LEAK SEALER BLACK (IN TINS)-89242 NPD10543

## Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Decomposition temperature	: Not available
pH	: Not available
Viscosity, kinematic	: Not available
Solubility	: Not available
Partition coefficient n-octanol/water (Log Kow)	: Not available
Vapour pressure	: Not available
Vapour pressure at 50°C	: Not available
Density	: Not available
Relative density	: Not available
Relative vapour density at 20°C	: Not available
Particle characteristics	: Not applicable

### 9.2. Other information

#### 9.2.1. Information with regard to physical hazard classes

No additional information available

#### 9.2.2. Other safety characteristics

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Flammable liquid and vapour.

### 10.2. Chemical stability

Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

### 10.4. Conditions to avoid

Avoid contact with hot surfaces. Heat. No flames, no sparks. Eliminate all sources of ignition.

### 10.5. Incompatible materials

No additional information available

### 10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## SECTION 11: Toxicological information

### 11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified
Skin corrosion/irritation	: Not classified
Serious eye damage/irritation	: Not classified
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
STOT-single exposure	: May cause drowsiness or dizziness.

#### Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics

STOT-single exposure	May cause drowsiness or dizziness.
----------------------	------------------------------------

# JENOLITE STOP LEAK SEALER BLACK (IN TINS)-89242 NPD10543

## Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

STOT-repeated exposure : Not classified  
Aspiration hazard : Not classified

### 11.2. Information on other hazards

No additional information available

## SECTION 12: Ecological information

### 12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.  
Hazardous to the aquatic environment, short-term (acute) : Not classified  
Hazardous to the aquatic environment, long-term (chronic) : Not classified  
Not rapidly degradable

### 12.2. Persistence and degradability

No additional information available

### 12.3. Bioaccumulative potential

No additional information available

### 12.4. Mobility in soil

No additional information available

### 12.5. Results of PBT and vPvB assessment

No additional information available

### 12.6. Endocrine disrupting properties

No additional information available

### 12.7. Other adverse effects

No additional information available

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.  
Additional information : Flammable vapours may accumulate in the container.

## SECTION 14: Transport information


In accordance with ADR

ADR	
14.1. UN number or ID number	UN 1263
14.2. UN proper shipping name	PAINT RELATED MATERIAL
Transport document description	UN 1263 PAINT RELATED MATERIAL, 3, III, (D/E)

# JENOLITE STOP LEAK SEALER BLACK (IN TINS)-89242 NPD10543



## Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

ADR	
<b>14.3. Transport hazard class(es)</b>	
	3
	
<b>14.4. Packing group</b>	
	III
<b>14.5. Environmental hazards</b>	
	Dangerous for the environment: No
No supplementary information available	

### 14.6. Special precautions for user

#### Overland transport

Classification code (ADR)	: F1
Special provisions (ADR)	: 163, 367, 650
Limited quantities (ADR)	: 5I
Excepted quantities (ADR)	: E1
Packing instructions (ADR)	: P001, IBC03, LP01, R001
Special packing provisions (ADR)	: PP1
Mixed packing provisions (ADR)	: MP19
Portable tank and bulk container instructions (ADR)	: T2
Portable tank and bulk container special provisions (ADR)	: TP1, TP29
Tank code (ADR)	: LGBF
Vehicle for tank carriage	: FL
Transport category (ADR)	: 3
Special provisions for carriage - Packages (ADR)	: V12
Special provisions for carriage - Operation (ADR)	: S2
Hazard identification number (Kemler No.)	: 30
Orange plates	:  

Tunnel restriction code (ADR)	: D/E
EAC code	: •3Y

### 14.7. Maritime transport in bulk according to IMO instruments

Not applicable

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.1.1. EU-Regulations

##### REACH Annex XVII (Restriction List)

Contains no substance(s) listed on REACH Annex XVII (Restriction Conditions)

##### REACH Annex XIV (Authorisation List)

Contains no substance(s) listed on REACH Annex XIV (Authorisation List)

##### REACH Candidate List (SVHC)

Contains no substance(s) listed on the REACH Candidate List

# JENOLITE STOP LEAK SEALER BLACK (IN TINS)-89242 NPD10543

## Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

### PIC Regulation (Prior Informed Consent)

Contains no substance(s) listed on the PIC list (Regulation EU 649/2012 concerning the export and import of hazardous chemicals)

### POP Regulation (Persistent Organic Pollutants)

Contains no substance(s) listed on the POP list (Regulation EU 2019/1021 on persistent organic pollutants)

### Ozone Regulation (1005/2009)

Contains no substance(s) listed on the Ozone Depletion list (Regulation EU 1005/2009 on substances that deplete the ozone layer)

### Explosives Precursors Regulation (2019/1148)

Contains no substance(s) listed on the Explosives Precursors list (Regulation EU 2019/1148 on the marketing and use of explosives precursors)

### Drug Precursors Regulation (273/2004)

Contains no substance(s) listed on the Drug Precursors list (Regulation EC 273/2004 on the manufacture and the placing on market of certain substances used in the illicit manufacture of narcotic drugs and psychotropic substances)

## 15.1.2. National regulations

### France

Occupational diseases	
Code	Description
RG 84	Conditions caused by liquid organic solvents for professional use: saturated or unsaturated aliphatic or cyclic liquid hydrocarbons and mixtures thereof; liquid halogenated hydrocarbons; nitrated derivatives of aliphatic hydrocarbons; alcohols; glycols, glycol ethers; ketones; aldehydes; aliphatic and cyclic ethers, including tetrahydrofuran; esters; dimethylformamide and dimethylacetamine; acetonitrile and propionitrile; pyridine; dimethylsulfone and dimethylsulfoxide

### Germany

Employment restrictions : Observe restrictions according Act on the Protection of Working Mothers (MuSchG).  
Observe restrictions according Act on the Protection of Young People in Employment (JArbSchG).

Water hazard class (WGK) : WGK 3, Highly hazardous to water (Classification according to AwSV, Annex 1).

Hazardous Incident Ordinance (12. BImSchV) : Is not subject of the Hazardous Incident Ordinance (12. BImSchV)

### Netherlands

SZW-lijst van kankerverwekkende stoffen : None of the components are listed

SZW-lijst van mutagene stoffen : None of the components are listed

SZW-lijst van reprotoxische stoffen – Borstvoeding : None of the components are listed

SZW-lijst van reprotoxische stoffen – Vruchtbaarheid : None of the components are listed

SZW-lijst van reprotoxische stoffen – Ontwikkeling : None of the components are listed

### Denmark

Classification remarks : Emergency management guidelines for the storage of flammable liquids must be followed

Danish National Regulations : Young people below the age of 18 years are not allowed to use the product

### Switzerland

Storage class (LK) : LK 3 - Flammable liquids

## 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

## SECTION 16: Other information

Abbreviations and acronyms:	
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate



# JENOLITE STOP LEAK SEALER BLACK (IN TINS)-89242 NPD10543

## Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Abbreviations and acronyms:	
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
COD	Chemical oxygen demand (COD)
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
EN	European Standard
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
VOC	Volatile Organic Compounds
CAS-No.	Chemical Abstract Service number
N.O.S.	Not Otherwise Specified
vPvB	Very Persistent and Very Bioaccumulative
ED	Endocrine disrupting properties

Full text of H- and EUH-statements:	
Asp. Tox. 1	Aspiration hazard, Category 1
Flam. Liq. 3	Flammable liquids, Category 3
H226	Flammable liquid and vapour.
H304	May be fatal if swallowed and enters airways.
H336	May cause drowsiness or dizziness.

# JENOLITE STOP LEAK SEALER BLACK (IN TINS)-89242 NPD10543

## Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

### Full text of H- and EUH-statements:

STOT SE 3	Specific target organ toxicity – Single exposure, Category 3, Narcosis
-----------	--

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.