

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2135231011](#)
Status: **Active**
Overview: [LTE Cellular Antennas](#)
Description: 698MHz-2.7GHz LTE Hinged External Antenna, with Reverse Polar SMA Male Connector, White

Documents:

3D Model	Application Specification 2135230001-000 (PDF)
3D Model (PDF)	Packaging Specification 2135230001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 2135230001-001 (PDF)	



General

Product Family	Antennas
Series	213523
Component Type	External Antenna
Function	Signal
Mates With	Reverse Polar SMA Female Receptacle
Overview	LTE Cellular Antennas
Product Name	LTE Cellular Antenna
Protocol	Cellular
Type	External Antenna
UPC	193264424573

Physical

Length	171.50mm
Mounting Style	N/A
Net Weight	14.143/g
Packaging Type	PET Bag
Polarization	Linear
Radiation Pattern	Omnidirectional
Width	19.40mm

Electrical

Band#1 F_End (MHz)	960
Band#1 F_Start (MHz)	698
Band#2 F_End (MHz)	2690
Band#2 F_Start (MHz)	1710
Electrical Connectivity	Cable
Peak Gain (dBi)	2.3 @ 698 MHz, 4.8 @ 1710 MHz
Return Loss - S11 (dB)	< -10, < -5
Total Efficiency	>55% @ 698 MHz, >70% @ 1710 MHz

Material Info

Reference - Drawing Numbers

Application Specification	2135230001-000
Packaging Specification	2135230001-001
Product Specification	2135230001-001
Sales Drawing	2135230001-000

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ECHA_01_2020 (16 January 2020)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[213523 Series](#)