

PSSN clamp holder with internal cooling, negative

for facing and longitudinal turning using SN indexable inserts

ATORN®

Application

for copy turning and longitudinal turning using SN indexable insert 90°.

Version

- precision-manufactured steel support with high-performance internal cooling system, nickel-plated, hardened, adjustable clamping system, type D, working angle 45°, tip angle 90°, clearance angle 0°

Advantage

- high-performance cooling channel system with three outlets ensures an extremely long service life and reliable work
- triple-edge geometry lowers cost per cut
- negative body geometry ensures good stability and absorption of force for large cutting depths



Art. no.	17840 106
ISO name	PSSN R/L 2525 M12 IK G1/8
Shaft height	25 mm
Shank width	25 mm
Length	150 mm
Length of head	29.3 mm
Programming size	32 mm
Suitable for indexable inserts	SN.. 1204..
Tool design	Left

EAN-Code

405029344989 1