

## Revolving lathe point

**ORION**<sup>®</sup>

### Execution:

- Tip angle 60°.
- Moving point is hardened and can be reground multiple times.

### Advantage:

- Precision roller bearings ensure a high level of concentricity.
- Special seal prevents the ingress of dirt and coolant.
- Maintenance-free owing to permanent lubrication.

### Delivery:

1x revolving centring point.



<b>Art. no.</b>	<b>22124 140</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	22124140
<b>Morse taper size</b>	MK 4
<b>Programming size</b>	103 mm
<b>Programming size for housing</b>	61.5 mm
<b>Max. workpiece weight</b>	800 kg
<b>Max. rotation speed</b>	3800 rpm
<b>Concentricity tolerance</b>	0.005 mm
<b>Diameter of housing</b>	70 mm
<b>Tip diameter</b>	32 mm
<b>Gross Weight</b>	1.991 kg
<b>Product Group</b>	211

### EAN

4039247404025