


DO NOT SCALE DRAWING

REVISIONS

ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	DRAWN	22-10-2018	



Part No.	A
TRCBS-3-01	4.8
TRCBS-4-01	6.4
TRCBS-5-01	7.9
TRCBS-6-01	9.5
TRCBS-7-01	11.1
TRCBS-8-01	12.7
TRCBS-10-01	15.9
TRCBS-12-01	19.1
TRCBS-14-01	22.2
TRCBS-16-01	25.4
TRCBS-18-01	28.6
TRCBS-20-01	31.7
TRCBS-22-01	34.9

NOTES :

- Also available in flame retardant nylon(PA66 UL94V-0);
- Top Hole:  $\text{Ø}4.75 \pm 0.08\text{mm}$ , Panel Thickness: 0.79-1.98mm;
- Bottom Hole:  $\text{Ø}4.0 \pm 0.08\text{mm}$ , Panel Thickness: 1.57mm.

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN MILLIMETERS.  
SURFACE FINISH:  
TOLERANCES:  
 $L \leq 4 = \pm 0.1$   $4 < L \leq 15 = \pm 0.2$   
 $15 < L \leq 50 = \pm 0.3$   $50 < L \leq 100 = \pm 0.4$

MATERIAL  
PA66 UL94V-2  
ROHS COMPLIANT

TITLE  
PCB SUPPORT

NAME	DATE
DRAWN MARTIN ELLIOTT	22/10/2018
CHK'D	
APP'VD	

HEAT TREATMENT  
N/A

DESIGN RIGHT. TR FASTENINGS LTD. 2003  
UNDER NO CIRCUMSTANCES MUST THIS  
DRAWING BE COPIED OR DISCLOSED.  
WITHOUT FIRST OBTAINING WRITTEN  
AUTHORITY.

CUSTOMER PART NO.

FINISH  
NATURAL

DWG NO.  
TRCBS-XX-01

A3